

**Mini (7/8) 3 pole, Receptacle, Female (Int.) Straight,**

1/2" NPT, PVC, IEC Colors, 16AWG, 2 m

Art.No.: MURE-3FR-2M

Weight: 0.143 kg

Country of origin: US


Model designation: MIN-4FR-3-ME

7/8" (female)


Flange female

3-pole

with multi-strand wire

**[Link to Product](#)****Illustration**

Product may differ from Image



Cable length

R-,2M m

**Side 1**

Tightening torque	1,5 Nm
Mounting method	inserted, screwed
Coating contact	gold plated
Family construction form	7/8"
Thread	7/8"
No. of poles	3
Degree of protection (EN IEC 60529)	IP67

#### Commercial data

ECLASS-6.0	27279220
ECLASS-6.1	27279220
ECLASS-7.0	27440103
ECLASS-8.0	27440103
ECLASS-9.0	27440103
ECLASS-10.1	27440103
ECLASS-11.1	27440103
ECLASS-12.0	27440103
ETIM-5.0	EC001855
ETIM-6.0	EC001855
ETIM-7.0	EC001855
ETIM-8.0	EC001855
customs tariff number	85444290
customs tariff number	85444290
EAN	4048879738743
EAN	4048879738743
Packaging unit	1
Packaging unit	1

#### Electrical data | Supply

Operating voltage AC max.	600 V
Operating voltage DC max.	600 V
Current operating per contact max.	13 A

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed

#### Mechanical data | Material data

Material housing	Zinc die-casting
Coating housing	nickel plated
Material gasket	NBR

#### Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	105 °C
Additional condition temperature range	depending on cable quality

#### Important installation notes

Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	<b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.