

Mico Pro Power module

IN: 24 V DC / 40A, 16mm² / Cover plate included (heavy duty)

Art.No.: 9000-41190-0000000

Weight: 0.193 kg

Country of origin: CZ

Model designation: Mico Pro PM 24VDC/40A

Mico Pro® PM 24 V DC/40 A

Cover plate included (heavy duty)

Shock load


1/2 sin 40 g, 11 ms

Build your own Mico Pro® online:

[START](#)

Link to Product

Illustration



Product may differ from Image



Commercial data

URL Webshop

<https://shop.murrelektronik.com/9000-41190-0000000>

GTIN	4048879552080
Customs tariff number	85363030
ECLASS-6.0	27371802
ECLASS-6.1	27371890
ECLASS-7.0	27371890
ECLASS-7.1	27371890
ECLASS-8.0	27371890
ECLASS-8.1	27371890
ECLASS-9.0	27371802
ECLASS-9.1	27371890
ECLASS-10.0.1	27371892
ECLASS-10.1	27371802
ECLASS-11.0	27371892
ECLASS-11.1	27371802
ECLASS-12.0	27371802
ECLASS-13.0	27371892
ECLASS-14.0	27371892
ETIM-5.0	EC001440
ETIM-6.0	EC001440
ETIM-7.0	EC001440
ETIM-8.0	EC001440
customs tariff number	85363030
EAN	4048879552080
Packaging unit	1

Electrical data | Supply

Total current max.	40 A
--------------------	------

Electrical data | Input

Input voltage DC min.	9 V
Input voltage DC max.	30 V
Nominal input voltage DC	12 V ... 24 V
Total current bridge set max.	40 A
ON input voltage control inputs min.	9 V
ON input voltage control inputs max.	30 V
CTRL signal	ON/OFF
CTRL input voltage control inputs high min.	9 V
CTRL input voltage control inputs high max.	30 V
ON pulse length control inputs high min.	120 ms

Electrical data | Output

Switching voltage AC max.	30 V
Switching voltage DC max.	30 V

Installation

Connection cross-section static min.	0,75 mm ²
Connection cross section static max.	16 mm ²
Connection cross-section dynamic min.	0,75 mm ²
Connection cross section dynamic max.	16 mm ²
AWG number static min.	4
AWG number static max.	20
AWG number dynamic min.	4
AWG number dynamic max.	20

Installation | Connection

Connection	Bridge system
------------	---------------

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Device protection | Mechanical

Shock resistance (EN IEC 60068-2-27) 40 g 11 ms 1/2 sin

Mechanical data | Mounting data

Height 130 mm

Width 24 mm

Depth 114 mm

Mounting method geschnappt

Suitable for mounting type Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min. -25 °C

Operating temperature max. 55 °C

Ambient temperature (storage, transport) -40 °C ... 80 °C

Connection type 7

Family construction form Bridging Contact

No. of poles 1

Gender female

Color contact carrier black

PIN 1 UB In + 24 V DC

Family construction form Bridging Contact

No. of poles 1

Gender female

Color contact carrier black

PIN 1 0 V

Family construction form Bridging Contact

No. of poles 4

Gender female

Color contact carrier black

PIN 1 On

PIN 2 Ctrl

PIN 3 Alarm

PIN 4 0.9

Family construction form Bridging Contact

No. of poles 4

Gender female

Color contact carrier black

PIN 1 On

PIN 2 Ctrl

PIN 3 Alarm

PIN 4 0.9

Family construction form terminal

No. of poles 2

Gender female

Color contact carrier green

Connection Spring clamp terminals FK

PIN 1 13 Alarm

PIN 2 14 Alarm

Family construction form terminal

No. of poles 2

Gender female

Color contact carrier green

Connection Spring clamp terminals FK

PIN 1	23 90%
PIN 2	24 90%
Family construction form	terminal
No. of poles	2
Gender	female
Color contact carrier	green
Connection	Spring clamp terminals FK
PIN 1	Ctrl
PIN 2	On