

## MEF EMC-FILTER 3-PHASE 1-STAGE

I:110A U:3x600 VAC book-style

Current: 110 A


1-stage

Attenuation curves on request.

The MEF 3/1-3/2 3-phase and 1-/2-stage mains suppression filters are used in the 0.1...30 MHz range to suppress conducted interference on mains and supply lines. They are suitable for TN-C networks. The best filter effect is achieved with short connecting lines (recommendation: PE connection < 10 cm) with the largest possible cross sections. Line suppression filters act bidirectionally (in both directions). They reduce symmetrical and asymmetrical interference, which often occurs with frequency converters and switched-mode power supplies.

### [Link to Product](#)

#### Illustration



Product may differ from Image



#### Commercial data

ECLASS-6.0	27130806
ECLASS-6.1	27420201

ECLASS-7.0	27420290
ECLASS-8.0	27420290
ECLASS-9.0	27420290
ECLASS-10.1	27420208
ECLASS-11.1	27420208
ECLASS-12.0	27420208
ETIM-5.0	EC002498
customs tariff number	85363030
GTIN	4048879029193
Packaging unit	1

#### Electrical data

Leakage current max.	10 mA @ 250 V AC, 50 Hz
----------------------	-------------------------

#### Electrical data | Supply

Power frequency	50 ... 60 Hz
Operating voltage AC max.	600 V

#### Electrical data | Input

Phase number input	3
--------------------	---

#### Electrical data | Output

Overload current	18× (IN t) max. 0.5 ms; 1.5× (IN t) max. 1 min. (1× per hour)
------------------	---

#### Installation

Connection cross-section solid min.	16 mm²
Connection cross-section solid max.	50 mm²
Connection cross-section stranded/fine-stranded min.	16 mm²
Connection cross-section stranded/fine-stranded max.	50 mm²
AWG number solid min.	5
AWG number solid max.	0
AWG number stranded/fine stranded min.	5
AWG number stranded/fine stranded max.	0

#### Device protection | Electrical

Duration insulation test voltage	2 s
Insulation test voltage L-L	3,1 kV
Insulation test voltage L-N	3,3 kV

#### Mechanical data | Mounting data

Mounting method	screwed
Height	270 mm
Width	90 mm
Depth	150 mm

#### Environmental characteristics | Climatic

Climatic category (EN IEC 60068-1)	25/085/21
------------------------------------	-----------

#### Connection type 2

Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	gray
No. of poles	3
PIN 1	L 1
PIN 2	L 2
PIN 3	L 3
Connection	Screw terminals SK

Family construction form	terminal
Gender	female
Color contact carrier	gray
No. of poles	3
PIN 1	L 1'
PIN 2	L 2'
PIN 3	L 3'