

IMPACT67 Pro PN DIO8 IOL8 M12L 5P

PROFINET, compact module, plastic


Digital inputs/outputs
Ethernet 10/100 Mbit/s; M12, D-coded
IO-Link V1.1
M12 Power, 5-pole, L-coded
M12, 5-pole, A-coded
Housing fully potted.
Connection cables are in the online shop under "Connection Technology".
mounting compatible with I/O modules of the MVK series

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|--------------------------|---------------|
| ECLASS-6.0 | 27242604 |
| ECLASS-6.1 | 27242604 |
| ECLASS-7.0 | 27242604 |
| ECLASS-8.0 | 27242604 |
| ECLASS-9.0 | 27242604 |
| ECLASS-10.1 | 27242604 |
| ECLASS-11.1 | 27242604 |
| ECLASS-12.0 | 27242604 |
| ETIM-5.0 | EC001599 |
| customs tariff number | 85389099 |
| GTIN | 4048879859929 |
| Packaging unit | 1 |
| Electrical data Supply | |
| Norm operating voltage | EN 61131-2 |
| Operating voltage US DC | 24 V |
| Operating voltage UA DC | 24 V |
| Total current UA max. | 16 A |

Total current US max. 16 A

Electrical data | Input

| | |
|----------------------------------|---|
| Overload resistant | yes |
| Short-circuit protected | yes |
| Type input | PNP, for 3-wire sensors or mechanical switches, IO-Link Devices |
| Sensor current US per input max. | 2 A |
| Current carrying capacity max. | 10 A |

Electrical data | Output

| | |
|-------------------------------------|------|
| Actuator current UA per output max. | 2 A |
| Overload resistant | yes |
| Short-circuit protected | yes |
| Output current per pin max. | 2 A |
| Max. current output per port | 4 A |
| Total current output max. | 10 A |

Industrial communication

| | |
|--------------------|----------|
| Supported protocol | PROFINET |
| Web interface | yes |

Industrial communication | Profinet

| | |
|---|------|
| Number of active connections (IO controller) max. | 2 |
| IRT (network communication) | yes |
| PROFINET Netload Class | III |
| PROFINET addressing | DCP |
| PROFINET conformance class | C |
| PROFINET specification | V2.3 |
| Shared device/input | yes |

Industrial communication | IO-Link

| | |
|------------------------------------|------------------|
| Automatic baudrate detection | yes |
| IO-Link process data length output | 32 Bytes |
| IO-Link process data length input | 32 Bytes |
| IO-Link type | 8x Master |
| IO-Link transmission rate | COM1, COM2, COM3 |
| Port Class | A, B |

Industrial communication | IIoT functions

| | |
|--|--|
| Number of sessions / clients OPC UA max. | 5 |
| JSON integration | REST-API, MQTT |
| OPC UA transport | UA TCP, UA Secure Conversation, UA Binary Encoding |
| Voltage monitoring | yes |
| Current Monitoring | yes |
| Publishing interval OPC UA min. | 100 ms |

Diagnostics

| | |
|---------------------|----------------------------------|
| Actuator warning | per channel via LED and BUS |
| Diagnostic via BUS | per module and channel |
| Diagnostic via LED | per module and channel |
| IO-Link events | No voltage, Undervoltage supply |
| LED display | Ethernet connection/data traffic |
| Cable break | per port |
| Temperature control | yes |

Device protection | Electrical

| | |
|-------------------------------------|------|
| Degree of protection (EN IEC 60529) | IP67 |
|-------------------------------------|------|

Mechanical data | Mounting data

| | |
|----------------------------|-----------------------|
| Suitable for mounting type | 2-hole screw mounting |
| Height | 37 mm |
| Width | 63 mm |
| Depth | 225 mm |

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | -40 °C |
| Operating temperature max. | 70 °C |
| Storage temperature min. | -40 °C |
| Storage temperature max. | 80 °C |

Connection type 4

| | |
|--------------------------|-------------------|
| Connection type 1 | X0-X7 |
| Connection type 2 | XD1 |
| Connection type 3 | XD2 |
| Connection type 4 | XF1, XF2 |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | gray |
| Coding | A |
| No. of poles | 5 |
| PIN 1 | 24 V DC |
| PIN 2 | DI / DO |
| PIN 3 | 0 V |
| PIN 4 | DI / DO / IO-Link |
| PIN 5 | 0 V |
| Family construction form | M12 |
| Gender | male |
| Color contact carrier | black |
| Coding | L |
| No. of poles | 5 |
| PIN 1 | 24 V DC (US) |
| PIN 2 | 0 V |
| PIN 3 | 0 V |
| PIN 4 | 24 V DC (UA) |
| PIN 5 | PE |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | black |
| Coding | L |
| No. of poles | 5 |
| PIN 1 | 24 V DC (US) |
| PIN 2 | 0 V |
| PIN 3 | 0 V |
| PIN 4 | 24 V DC (UA) |
| PIN 5 | PE |
| Mounting method | inserted, screwed |
| Tightening torque | 0,6 Nm |
| Family construction form | M12 |
| Gender | female |
| Color contact carrier | black |
| Coding | D |
| No. of poles | 4 |
| PIN 1 | TD + |
| PIN 2 | RD + |

| | |
|-------|------|
| PIN 3 | TD - |
| PIN 4 | RD - |