

MVK I/O COMPACT MODULE, METAL

CANopen, 16 dig. In / Diag

Digital inputs

DI8 DI8

CAN 1 Mbit/s; M12, A-coded

7/8", 5-pole, 2× max. 9 A

M12, 5-pole, A-coded

Connection cables are in the online shop under "Connection Technology".


Housing fully potted.

Link to Product

Illustration



Product may differ from Image



Input

Sensor supply US	24 V DC (EN 61131-2), max. 200 mA (M12 female), short-circuit and overload protected
Type	for 3-wire sensors or mechanical switches, PNP

General data

Mounting method	2-hole screw mounting
Temperature range	0...+55 °C (storage temperature -20...+70 °C)
Protection	IP67
Dimensions H×W×D	42×63×225 mm

Module supply

Operating voltage	24 V DC (EN 61131-2)
-------------------	----------------------

Diagnostic

Communication status	via LED
Diagnostic via BUS	per module and channel
Diagnostic via LED	per module and channel
Actuator warning	per channel via LED and BUS
Monitoring - under voltage	yes
Monitoring - no voltage	yes
Short-circuit and overload	yes

Cable break	per port
-------------	----------

CANopen

Addressing	Rotary switch 1...99
------------	----------------------

Connections

Fieldbus	CAN 1 Mbit/s; M12, A-coded
----------	----------------------------

Sensor-system/actuator supply	7/8", 5-pole, 2× max. 9 A
-------------------------------	---------------------------

I/O ports	M12, 5-pole, A-coded
-----------	----------------------

Parameterization

PIN 4	Input
-------	-------

PIN 2	Input/Diagnostic
-------	------------------