

MVK+ MPNIO DI8 DI8 IRT PUSH PULL

MVK ProfiNet, metal, galvanic separation


Digital inputs  
DI8 DI8 (IRT)  
Ethernet 10/100 Mbit/s; Push Pull RJ45 Data connector  
Push Pull Power connector, max. 12 A  
M12, 5-pole, A-coded  
Galvanic isolation  
Connection cables are in the online shop under "Connection Technology".  
Housing fully potted.

Link to Product

Illustration



Product may differ from Image



Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27242604      |
| ECLASS-6.1            | 27242604      |
| ECLASS-7.0            | 27242604      |
| ECLASS-8.0            | 27242604      |
| ECLASS-9.0            | 27242604      |
| ECLASS-10.1           | 27242604      |
| ECLASS-11.1           | 27242604      |
| ECLASS-12.0           | 27242604      |
| ETIM-5.0              | EC001599      |
| customs tariff number | 85389099      |
| GTIN                  | 4048879461672 |
| Packaging unit        | 1             |

Electrical data | Supply

|                         |            |
|-------------------------|------------|
| Norm operating voltage  | EN 61131-2 |
| Operating voltage US DC | 24 V       |
| Total current UA max.   | 12 A       |
| Total current US max.   | 12 A       |

| Electrical data   Input                           |  |
|---|--|
| Overload resistant                                | yes  |
| Short-circuit protected                           | yes  |
| Type input  | PNP, for 3-wire sensors or mechanical switches |
| Sensor current US per input max.                  | 0,2 A  |
| Industrial communication                          |  |
| Supported protocol                                | PROFINET                                       |
| Industrial communication   Profinet               |  |
| Number of active connections (IO controller) max. | 2  |
| FSU (Fast-Start-Up)                               | yes  |
| Fast start up time max.                           | 0,5 s  |
| IRT (network communication)                       | yes  |
| MRP client  | yes  |
| PROFINET Netload Class                            | III  |
| PROFINET addressing                               | DCP  |
| PROFINET conformance class                        | C  |
| PROFINET specification                            | V2.2   |
| Shared device/input                               | yes  |
| Diagnostics                                       |  |
| Actuator warning                                  | per channel via LED and BUS                    |
| Diagnostic  | No voltage, Under voltage                      |
| Diagnostic via BUS                                | per module and channel                         |
| Diagnostic via LED                                | per module and channel                         |
| Short circuit diagnosis                           | yes  |
| LED display                                       | Ethernet connection/data traffic               |
| Cable break                                       | per port                                       |
| Overload diagnosis                                | yes  |
| Device protection   Electrical                    |  |
| Degree of protection (EN IEC 60529)               | IP67   |
| Mechanical data   Mounting data                   |  |
| Suitable for mounting type                        | 2-hole screw mounting                          |
| Height  | 42,7 mm  |
| Width   | 63 mm  |
| Depth   | 225 mm   |
| Environmental characteristics   Climatic          |  |
| Operating temperature min.                        | 0 °C   |
| Operating temperature max.                        | 55 °C  |
| Storage temperature min.                          | -20 °C   |
| Storage temperature max.                          | 70 °C  |
| Connection type 3                                 |  |
| Connection type 1                                 | X4-X7  |
| Connection type 2                                 | XD1, XD2                                       |
| Connection type 3                                 | XF1, XF2                                       |
| Family construction form                          | M12  |
| Gender  | female   |
| Color contact carrier                             | black  |
| Coding  | A  |
| No. of poles                                      | 5  |
| PIN 1   | 24 V DC (US)                                   |
| PIN 2   | DI   |

|                          |              |
|--------------------------|--------------|
| PIN 3                    | 0 V (US)     |
| PIN 4                    | DI           |
| PIN 5                    | PE           |
| Family construction form | Push Pull    |
| Gender                   | male         |
| Color contact carrier    | green        |
| No. of poles             | 5            |
| PIN 1                    | 24 V DC (US) |
| PIN 2                    | 0 V (US)     |
| PIN 3                    | 24 V DC (UA) |
| PIN 4                    | 0 V (UA)     |
| PIN 5                    | PE           |
| Family construction form | RJ45         |
| Gender                   | female       |
| Color contact carrier    | black        |
| No. of poles             | 8            |
| PIN 1                    | TD +         |
| PIN 2                    | TD -         |
| PIN 3                    | RD +         |
| PIN 4                    | n.c.         |
| PIN 5                    | n.c.         |
| PIN 6                    | RD -         |
| PIN 7                    | n.c.         |
| PIN 8                    | n.c.         |