MURR ELEKTRONIK
stay connected

Gateway Ethernet-IP/AS-i, 1 Master, P24


Spec. 3.0, Diagnosis Field bus, Power 24

AS-Interface/EtherNet/IP
Power 24V
Specification 3.0
Diagnostic via BUS
Current manuals, GSD/type data can be downloaded at: www.murrelektronik.com
Other gateways on request.
Gateway-Singlemaster
AS-Interface data decoupling integrated
AS-Interface duplicate address detection
AS-Interface EMC detector integrated

Link to Product

Illustration





Product may differ from Image

Commercial data

ECLASS-6.0	27242208
ECLASS-6.1	27242608
ECLASS-7.0	27242608
ECLASS-8.0	27242608
ECLASS-9.0	27242608
ECLASS-10.1	27242608
ECLASS-11.1	27242608
ECLASS-12.0	27242608
ETIM-5.0	EC001604
customs tariff number	85176200
GTIN	4048879496674
Packaging unit	1

Electrical data

Rated operating current AS-Interface max.	250 mA
Security level	PELV

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28

MURR ELEKTRONIK
stay connected

Electrical data | Supply	
Operating voltage DC	24 V
Operating voltage DC min.	20 V
Operating voltage DC max.	30,6 V
Industrial communication	
Supported protocol	EtherNet/IP
Industrial communication | AS-Interface	
AS-i specification	V3.0
Number of slaves max.	62
Diagnostic interface serial	RJ45/Fieldbus
Cycle time AS-i	150 µs × (number of slaves + 2)
Installation | Connection	
Family construction form	RJ45
Device protection | Electrical	
Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	500 V
Mechanical data | Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	120 mm
Width	85 mm
Depth	83 mm
Environmental characteristics | Climatic	
Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Conformity	
Product standard	EN 61131-2, EN 62026-2

The information in this Product-PDF has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-03-28