

S-Switch 22 2NO 1x40SR M12(4)

Select switch 1x40° spring return


S-Switch 22 2NO 2x40SR M12(4)  
Select switch 1x40° spring return  
Mounting hole 22,3 mm  
Connection M12 (4-pin)

Link to Product

Illustration



Product may differ from Image



| Commercial data               |               |
|-------------------------------|---------------|
| ECLASS-6.1                    | 27371243      |
| ECLASS-7.0                    | 27371243      |
| ECLASS-8.0                    | 27371243      |
| ECLASS-9.0                    | 27371243      |
| ECLASS-10.1                   | 27371243      |
| ECLASS-11.1                   | 27371243      |
| ECLASS-12.0                   | 27371243      |
| ETIM-5.0                      | EC001029      |
| customs tariff number         | 85365080      |
| GTIN                          | 4048879880763 |
| Packaging unit                | 1             |
| Electrical data   Supply      |               |
| Rated operating voltage AC-15 | 35 V          |
| Rated operating voltage DC-13 | 35 V          |
| Rated operating current       | 0,1 A         |
| Electrical data   Input       |               |
| Short-circuit current         | 1000 A        |
| Electrical data   Output      |               |
| Switching power max.          | 0,25 W        |
| Voltage switching AC min.     | 1 V           |

|                                      |        |
|--------------------------------------|--------|
| Switching voltage AC max.            | 32 V   |
| Switching voltage AC max. (UL 60947) | 30 V   |
| Voltage switching DC min.            | 1 V    |
| Switching voltage DC max.            | 32 V   |
| Switching voltage DC max. (UL 60947) | 30 V   |
| Switching current min.               | 1 mA   |
| Switching current max.               | 100 mA |

#### Installation | Connection

|                          |     |
|--------------------------|-----|
| Family construction form | M12 |
|--------------------------|-----|

#### Installation | Pin assignment

|              |   |
|--------------|---|
| Coding       | A |
| No. of poles | 4 |

#### Device protection | Electrical

|                                           |                                      |
|-------------------------------------------|--------------------------------------|
| Installation height max. ASL              | 2000 m                               |
| Degree of protection front (EN IEC 60529) | IP65                                 |
| Degree of protection back (EN IEC 60529)  | IP65                                 |
| Pollution Degree                          | 2                                    |
| Short circuit protective device (SCPD)    | fuse 250 V / 0.1 A / 1.5 kA gG quick |
| Rated insulation voltage                  | 250 V                                |
| Overvoltage category (EN 60950-1)         | II                                   |

#### Device protection | Mechanical

|                                     |               |
|-------------------------------------|---------------|
| Mechanical endurance                | 200000 Cycles |
| Mechanical endurance B10            | 250000 Cycles |
| UL enclosure type rating front side | type 4X       |

#### Device protection | Media

|                                        |     |
|----------------------------------------|-----|
| Salt-spray resistance (IEC 60068-2-11) | yes |
|----------------------------------------|-----|

#### Mechanical data

|                    |               |
|--------------------|---------------|
| Can be illuminated | no            |
| Actuating function | spring return |
| Color              | black         |
| Color bezel        | white         |
| Color collar       | black         |
| Color front ring   | black         |
| Shape collar       | round         |
| Contact type       | 2 S           |

#### Mechanical data | Material data

|                  |         |
|------------------|---------|
| Material housing | Plastic |
| Material contact | Gold    |

#### Mechanical data | Mounting data

|                     |               |
|---------------------|---------------|
| Mounting method     | Threaded ring |
| Installation height | 23,8 mm       |
| Mounting depth      | 36,4 mm       |
| Mounting hole       | 22,3 mm       |
| Height              | 29,8 mm       |
| Width               | 53,9 mm       |
| Grid min.           | 30 mm         |

#### Environmental characteristics | Climatic

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -40 °C |
| Operating temperature max. | 85 °C  |
| Derating from              | 40 °C  |
| Storage temperature min.   | -40 °C |

|                                    |        |
|------------------------------------|--------|
| Storage temperature max.           | 90 °C  |
| Relative humidity max. (operation) | 93 %   |
| <b>Connection type 1</b>           |        |
| Family construction form           | M12    |
| Gender                             | male   |
| Color contact carrier              | black  |
| Coding                             | A      |
| No. of poles                       | 4      |
| PIN 1                              | NO 1 2 |
| PIN 2                              | NO 1   |
| PIN 4                              | NO 2   |