

**MODLINK MSDD DATA INSERT**

1xSUB-D9 female/male + 1xSUB-D15 female/male

SUB-D9; SUB-D15

1× SUB-D9 (female/male)

1× SUB-D15 (female/male)

[Link to Product](#)**Illustration**

Product may differ from Image

**General data**

Dimensions HxWxD 88x51x40 mm

**SUB-D9**

Connection rear side	SUB-D (male)
Operating current (UL Rating)	max. 175 mA
Connection front side	SUB-D (female)
Locking of ports	UNC 4...40 bolt
Operating voltage (UL Rating)	max. 30 V AC/42.4 V DC
Operating current	3 A
No. of poles	9-pole
Operating voltage	48 V AC/DC

Product article number of manufacturer 4000-68000-0300000