

MODLINK MSDD DATA INSERT

1×SUB-D9 female/female + 1×RJ45 + 1×RJ12

RJ45; RJ12; SUB-D9  
1 × RJ45, 8-pole metal, CAT5e (female/female)  
1 × RJ12 (6-pole plastic)  
1 × SUB-D9 (female/female)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037679
Packaging unit	1
Mechanical data   Mounting data	
Height	88 mm
Width	51 mm
Depth	45 mm
Environmental characteristics   Climatic	
Storage temperature min.	-20 °C
Storage temperature max.	60 °C
Shielding plate	

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
<b>SUB-D9</b>	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D9
Family type Back side	SUB-D9
Gender	female
Gender Rear	female
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	9
<b>RJ12</b>	
Operating voltage AC max.	48 V
Operating voltage DC max.	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current max.	1 A
Current operating max. (UL)	175 mA
Family construction form	RJ12
Family type Back side	RJ12
Looking techniques	Snap-in connector
<b>RJ45</b>	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector