



**M12 MALE 0° DIAGNOSTIC PLUG DESINA**


Blind plug diagnostic M12×1 mm  
Bridge PIN 1 + 2

[Link to Product](#)

Illustration



Product may differ from Image



| Commercial data |          |
|-----------------|----------|
| ECLASS-6.0      | 23111190 |
| ECLASS-6.1      | 27260702 |
| ECLASS-7.0      | 27440390 |
| ECLASS-8.0      | 27440190 |
| ECLASS-9.0      | 27440190 |
| ECLASS-10.1     | 27440190 |
| ECLASS-11.1     | 27440190 |
| ECLASS-12.0     | 27440190 |
| ETIM-5.0        | EC001855 |

|  |                                       |
|--|---------------------------------------|
| customs tariff number                  | 85366990                              |
| GTIN                                   | 4048879198745                         |
| Packaging unit                         | 1                                     |
| <b>Electrical data   Supply</b>        |                                       |
| Operating voltage AC max.              | 30 V                                  |
| Operating voltage DC max.              | 30 V                                  |
| Operating voltage AC max. (UL-listed)  | 30 V                                  |
| Operating voltage DC max. (UL-listed)  | 30 V                                  |
| Current operating per contact max.     | 4 A                                   |
| <b>Installation   Connection</b>       |                                       |
| Tightening torque                      | 0,6 Nm                                |
| <b>Device protection   Electrical</b>  |                                       |
| Degree of protection (EN IEC 60529)    | IP67                                  |
| Additional condition protection degree | screwed, mounted                      |
| <b>Mechanical data   Material data</b> |                                       |
| Coating locking                        | Nickel                                |
| Locking material                       | Zinc die-casting                      |
| <b>Mechanical data   Mounting data</b> |                                       |
| Mounting method                        | inserted, screwed, Shaking protection |