




M12 gender-changer female / female D-cod.


Ethernet CAT5
Control cabinet entry system
Female - female
M12, 4-pole
D-coded
shielded

[Link to Product](#)**Illustration**

Female



Female



Product may differ from Image

EtherNet/IP

PROFI
NET

EtherCAT

Form

Form 44611

Technical Data

Operating voltage	max. 60 V AC/DC
Rated surge voltage	0.8 kV
Operating current per contact	max. 4 A
Transfer parameters	CAT5, Class D (ISO/IEC 11801:2002), (EN 50173-1)
Transfer rate	up to 100 Mbit/s full duplex
Coding	M12, D-coded

Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
Compression gland	M16 (SW19)
Protection	IP67 inserted and tightened (EN 60529)
Material	Brass, nickel plated

General data

Temperature range	-25...+85 °C
-------------------	--------------

Commercial data

country of origin	DE
customs tariff number	85366990
EAN	4048879140928
eClass	27279220
Packaging unit	1.000