


## Male module, 5-pole, Push-in

400 V, 16 A

Male 5-pole Push-In terminals Technical data will be only guaranteed with Murrelektronik components. Please use wire end ferrule. The clip 70MH-ZZ100-0000000 is needed (2×)

## Link to Product

Illustration



Product may differ from Image



27143424
27261204
27440204
27440204
27440217
27440217
27440217
27440217
EC000438
85366990
4048879664004
5
400 V
400 V
16 A
0,14 mm²

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-04-27

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com



Connection cross section max.	2,5 mm <sup>2</sup>
AWG number min.	26
AWG number max.	14
Installation   Connection	
Connection	Push-In spring clamp terminals
Gender	male
Mating cycles min.	500
Installation   Pin assignment	
No. of poles	5
Device protection   Electrical	
Pollution Degree	3
Rated surge voltage	6 kV
Overvoltage category (EN 60950-1)	III
Mechanical data   Material data	
Coating contact	silver-plated
Combustibility class (UL94)	V-0
Material housing	PC
Material contact	Brass
Mechanical data   Mounting data	
Number of module slots	1
Height	35,5 mm
Width	34,1 mm
Depth	14,6 mm
Environmental characteristics   Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	125 °C

The information in this Product-PDF has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-04-27

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com