

MOTOR SUPPRESSOR

Varistor, 3x575VAC/10kW


3× 575 V AC

VDR

Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.

Link to Product

Illustration



Product may differ from Image



| Commercial data |          |
|-----------------|----------|
| ECLASS-6.0      | 27371013 |
| ECLASS-6.1      | 27371013 |
| ECLASS-7.0      | 27371013 |
| ECLASS-8.0      | 27371013 |
| ECLASS-9.0      | 27371013 |
| ECLASS-10.1     | 27371013 |

|  |  |
|--|--|
| ECLASS-11.1  | 27371013   |
| ECLASS-12.0  | 27371013   |
| ETIM-5.0   | EC000197   |
| customs tariff number                                | 85363010   |
| GTIN   | 4048879019545  |
| Packaging unit                                       | 1  |
| <b>Electrical data   Supply</b>                      |  |
| Power frequency                                      | 10 ... 400 Hz  |
| <b>Electrical data   Input</b>                       |  |
| Input voltage AC                                     | 575 V  |
| <b>Installation</b>                                  |  |
| Connection cross-section stranded/fine-stranded min. | 0,5 mm <sup>2</sup>                                  |
| <b>Installation   Connection</b>                     |  |
| Connection information                               | Einzellitzen mit selbstsicherndem Gabelkabelschuh M4 |
| Length single strands                                | 250 mm   |
| <b>Device protection   Media</b>                     |  |
| Flame resistance                                     | flame retardant                                      |
| <b>Mechanical data   Material data</b>               |  |
| Combustibility class housing (UL94)                  | V-0  |
| Material housing                                     | Plastic  |
| Material potting compound                            | 2-component epoxy                                    |
| <b>Mechanical data   Mounting data</b>               |  |
| Height   | 75 mm  |
| Width  | 45 mm  |
| Depth  | 42 mm  |
| <b>Environmental characteristics   Climatic</b>      |  |
| Operating temperature min.                           | -20 °C   |
| Operating temperature max.                           | 60 °C  |