

RMI 24V AC/DC OUTPUT RELAY

IN: 24 VAC/DC - OUT: 250 VAC/DC / 15 A


1 relay; 1 NO/NC contact
15 A
24 V AC/DC
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-8.0	27371601
ECLASS-9.0	27371601
ECLASS-10.1	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
customs tariff number	85364900
GTIN	4048879027397
Packaging unit	1
Electrical data Input	
Input voltage AC min.	21,6 V
Input voltage AC max.	26,4 V
Input voltage DC min.	21,6 V
Input voltage DC max.	26,4 V
Electrical data Output	
Utilization category DC-13 (EN IEC 60947-5-1) 2 A @ 24 V, 0,3 A @ 110 V, 0,2 A @ 230 V	
Additional condition switching frequency	with load

Switching frequency max.	0,1 Hz
Power rating AC max.	4000 VA
Power rating DC max.	240 W
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	100 mA
Switching current max.	15 A
Switching capacity AC-12 (EN IEC 60947-5-1)	15 A (24 V AC; 230 V AC)
Switching capacity AC-15 (EN IEC 60947-5-1)	6 A (24 V AC; 230 V AC)

Diagnostics

Status indication LED	red
-----------------------	-----

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Rated surge voltage	6 kV
Electrical lifetime	20000000 Cycles

Device protection | Mechanical

Mechanical endurance	20000000 Cycles
----------------------	-----------------

Mechanical data

Drop-out time max.	15 ms
Response time max.	10 ms
Bounce time max.	2 ms

Mechanical data | Material data

Material contact	Ag Ni
------------------	-------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C

Connection type 2

Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	A 1
PIN 2	A 2
PIN 3	A 2
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	14
PIN 2	11
PIN 3	12