



MIRO 12.4 24-230V-1U OUTPUT RELAY

IN: 230 VAC/DC - OUT: 250 VAC/DC / 6 A


- 1 NO/NC contact
- 6 A
- 24 V DC, 24 V AC/DC, 48 V DC, 110 V AC/DC, 230 V AC/DC
- Screw terminals
- safe separation (EN 60947-1)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371001
ECLASS-6.1	27371601
ECLASS-7.0	27371601
ECLASS-8.0	27371601
ECLASS-9.0	27371601

ECLASS-10.1	27371601
ECLASS-11.1	27371601
ECLASS-12.0	27371601
ETIM-5.0	EC001437
customs tariff number	85364900
GTIN	4048879027014
Packaging unit	1

Electrical data | Input

Input voltage AC min.	21,6 V
Input voltage AC max.	253 V
Input voltage DC min.	21,6 V
Input voltage DC max.	253 V
Input current	6 mA
Control voltage AC min.	24 V
Control voltage AC max.	230 V
Control voltage DC min.	24 V
Control voltage DC max.	230 V

Electrical data | Output

Utilization category AC-12 (EN IEC 60947-5-1)	6 A @ 24, 6 A @ 110 V, 6 A @ 230 V
Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 24 V, 3 A @ 110 V, 3 A @ 230 V
Utilization category DC-13 (EN IEC 60947-5-1)	1 A @ 24 V, 0,2 A @ 110 V, 0,1 A @ 230 V
Switching frequency max.	10 Hz
Power rating AC max.	1500 VA
Power rating DC max.	120 W
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current DC	10 mA
Switching current max.	6 A

Diagnostics

Status indication LED	green
-----------------------	-------

Device protection

Condition lifetime	load-dependent
--------------------	----------------

Device protection | Electrical

Rated surge voltage	4 kV
Electrical lifetime	20000000 Cycles

Device protection | Mechanical

Mechanical endurance	20000000 Cycles
----------------------	-----------------

Mechanical data

Drop-out time max.	15 ms
Response time max.	10 ms
Bounce time max.	1,5 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	90 mm
Width	12,4 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	55 °C
----------------------------	-------

Connection type 3

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

No. of poles	2
--------------	---

PIN 1	11
-------	----

PIN 2	11
-------	----

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

No. of poles	2
--------------	---

PIN 1	12
-------	----

PIN 2	14
-------	----

Connection	Screw terminals SK
------------	--------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	green
-----------------------	-------

No. of poles	2
--------------	---

PIN 1	A 1
-------	-----

PIN 2	A 2
-------	-----