

PROFIBUS-PLUG-MALE (SUB-D) 90° WITH PG

Cut clamp for rigid and flexible wires

Bus connection plug 90°

PROFIBUS

SUB-D9 (male), IDC terminals, rigid and flexible cable, programming device connection

PROFIBUS, FC cable rigid/flexible, 1 × 2 × 0.64 mm², for outer diameter 8.0 ± 0.5 mm

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC001855
customs tariff number	85389091
GTIN	4048879050555
Packaging unit	1

Electrical data

Terminating resistor	connectable, integrated
----------------------	-------------------------

Electrical data | Supply

Operating voltage DC min.	4,75 V
Operating voltage DC max.	5,25 V
Current consumption max.	12,5 mA

Industrial communication

Data transmission rate max.	12 MBit/s
-----------------------------	-----------

Installation | Connection

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-04

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Connection	Cut clamps IDC
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Pollution Degree	2
Mechanical data Mounting data	
Height	72 mm
Width	40 mm
Depth	17 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	80 °C