

POTENTIAL TERMINAL BLOCK BROWN BLUE


Potential terminal block
brown/brown/blue/blue

Link to Product

Illustration



Product may differ from Image



| Commercial data | |
|--------------------------------|--------------------------------|
| ECLASS-6.0 | 27141106 |
| ECLASS-6.1 | 27141106 |
| ECLASS-7.0 | 27141106 |
| ECLASS-8.0 | 27141106 |
| ECLASS-9.0 | 27141106 |
| ECLASS-10.1 | 27141106 |
| ECLASS-11.1 | 27141106 |
| ECLASS-12.0 | 27141106 |
| ETIM-5.0 | EC001283 |
| customs tariff number | 85369010 |
| GTIN | 4048879049375 |
| Packaging unit | 1 |
| Electrical data Supply | |
| Operating voltage AC max. | 30 V |
| Operating voltage DC max. | 30 V |
| Total current max. | 10 A |
| Installation | |
| Connection cross section max. | 2,5 mm² |
| AWG number min. | 28 |
| AWG number max. | 14 |
| Installation Connection | |
| Connection | Spring clamp plug-in terminals |
| Device protection Electrical | |

Degree of protection (EN IEC 60529) IP20

Mechanical data | Mounting data

| | |
|--------|---------|
| Height | 70 mm |
| Width | 56 mm |
| Depth | 32,5 mm |

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | 0 °C |
| Operating temperature max. | 55 °C |
| Storage temperature min. | -40 °C |
| Storage temperature max. | 85 °C |