

## IMPACT20 PROFIBUS, DIGITAL INPUT MODULE

16 digital inputs

Digital inputs

DI16


Connection cables are in the online shop under "Connection Technology".

### [Link to Product](#)

#### Illustration



Product may differ from Image



#### Commercial data

ECLASS-6.0	27242604
ECLASS-7.0	27242604
ECLASS-8.0	27242604
ECLASS-9.0	27242604
ETIM-5.0	EC001599
customs tariff number	85389099
GTIN	4048879048101
Packaging unit	1

#### Electrical data | Supply

Operating voltage DC	24 V
Norm operating voltage	EN 61131-2
Operating voltage US DC	24 V
Total current UA max.	12 A

#### Electrical data | Input

Overload resistant	yes
Short-circuit protected	yes
Type input	PNP, for 3-wire sensors or mechanical switches
Current carrying capacity max.	0,7 A

#### Industrial communication | Bus data

Address range min.	3
Address range max.	99

The information in this Product-PDF has been compiled with the utmost care.  
 Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-21

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Address setting type

Rotary switch

**Diagnostics**

Diagnostic	No voltage, Under voltage
Diagnostic via BUS	per module
Diagnostic via LED	per module
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes

**Installation**

Connection cross section max.	2,5 mm <sup>2</sup>
-------------------------------	---------------------

**Device protection | Electrical**

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

**Mechanical data | Mounting data**

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	117 mm
Width	56 mm
Depth	47 mm

**Environmental characteristics | Climatic**

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-20 °C
Storage temperature max.	70 °C

**Conformity**

Product standard	EN 61131-2
------------------	------------

**Connection type 5**

Connection type 1	Bus In
Connection type 2	X0
Connection type 3	X1
Connection type 4	X2
Connection type 5	X3
Family construction form	D-Sub
Gender	female
Color contact carrier	white
No. of poles	9
PIN 1	n.c.
PIN 2	n.c.
PIN 3	B
PIN 4	n.c.
PIN 5	PE
PIN 6	5 V
PIN 7	n.c.
PIN 8	A
PIN 9	n.c.
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	colorless
No. of poles	6
PIN 1	CH 00
PIN 2	CH 01

PIN 3	CH 02
PIN 4	CH 03
PIN 5	UI
PIN 6	0 V
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	colorless
No. of poles	6
PIN 1	CH 10
PIN 2	CH 11
PIN 3	CH 12
PIN 4	CH 13
PIN 5	n.c.
PIN 6	0 V
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	colorless
No. of poles	6
PIN 1	CH 20
PIN 2	CH 21
PIN 3	CH 22
PIN 4	CH 23
PIN 5	US
PIN 6	0 V
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	colorless
No. of poles	6
PIN 1	CH 30
PIN 2	CH 31
PIN 3	CH 32
PIN 4	CH 33
PIN 5	FE
PIN 6	FE