

CUBE20S PROFINET IO BUS NODE


Bus nodes  
PROFINET Device

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27242608
ECLASS-6.1	27242608
ECLASS-7.0	27242608
ECLASS-8.0	27242608
ECLASS-9.0	27242608
ECLASS-10.1	27242608
ECLASS-11.1	27242608
ECLASS-12.0	27242608
ETIM-5.0	EC001604
customs tariff number	85389099
GTIN	4048879422406
Packaging unit	1
Electrical data   Supply	
Operating voltage DC	24 V
Current consumption max.	95 mA
Total current UA max.	10 A
Electrical data   Output	
Output voltage DC	24 V
Current output load supply max.	10 A
Current output backplane bus max.	3 A
Industrial communication	
Machine Option Management	yes
Supported protocol	PROFINET

Industrial communication   Bus data	
Address range outputs max.	512 Bytes
Address range inputs max.	512 Bytes
Industrial communication   Profinet	
Number of active connections (IO controller) max.	3
MRP client	yes
PROFINET addressing	DCP
PROFINET conformance class	B
PROFINET specification	V2.2
Shared device/input	yes
Diagnostics	
Actuator warning	no
Diagnostic	No voltage
Diagnostic via BUS	per module
Diagnostic via LED	per module and channel
Short circuit diagnosis	yes
LED display	Ethernet connection/data traffic
Overload diagnosis	yes
Installation	
Connection cross section max.	1,5 mm <sup>2</sup>
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data	
Number extension modules max.	64
Mechanical data   Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	109 mm
Width	48,5 mm
Depth	76,5 mm
Environmental characteristics   Climatic	
Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	70 °C
Conformity	
Product standard	EN 61131-2
Connection type 2	
Connection type 1	P2
Connection type 2	Power
Family construction form	RJ45
Gender	female
No. of poles	8
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 6	RD -
Connection	Spring clamp terminals FK
Family construction form	terminal

Gender	female
No. of poles	8
PIN 1	n.c.
PIN 2	24 V DC
PIN 3	0 V
PIN 4	24 V DC Sys
PIN 5	n.c.
PIN 6	24 V DC
PIN 7	0 V
PIN 8	0 V Sys