

CUBE20S POTENTIAL DISTRIBUTORS

4 x 24 V DC + 4 x 0 V DC


Potential distributor
Expansion module
4x 24 V DC

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27379201
ECLASS-6.1	27242611
ECLASS-7.0	27242611
ECLASS-8.0	27242611
ECLASS-9.0	27242611
ECLASS-10.1	27242611
ECLASS-11.1	27242611
ECLASS-12.0	27242611
ETIM-5.0	EC001600
customs tariff number	85369010
GTIN	4048879422871
Packaging unit	1
Electrical data Supply	
Operating voltage DC max.	30 V
Total current max.	10 A
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	109 mm

Width	12,9 mm
-------	---------

Depth	52,5 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	0 °C
----------------------------	------

Operating temperature max.	60 °C
----------------------------	-------

Storage temperature min.	-25 °C
--------------------------	--------

Storage temperature max.	70 °C
--------------------------	-------

Connection type 2

Connection type 1	Power
-------------------	-------

Connection type 2	Power
-------------------	-------

Connection	Spring clamp terminals FK
------------	---------------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

No. of poles	8
--------------	---

PIN 1	n.c.
-------	------

PIN 2	24 V DC
-------	---------

PIN 3	0 V
-------	-----

PIN 4	24 V DC Sys
-------	-------------

PIN 5	n.c.
-------	------

PIN 6	24 V DC
-------	---------

PIN 7	0 V
-------	-----

PIN 8	0 V Sys
-------	---------

Connection	Spring clamp terminals FK
------------	---------------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

No. of poles	8
--------------	---

PIN 1	24 V DC
-------	---------

PIN 2	24 V DC
-------	---------

PIN 3	24 V DC
-------	---------

PIN 4	24 V DC
-------	---------

PIN 5	0 V DC
-------	--------

PIN 6	0 V DC
-------	--------

PIN 7	0 V DC
-------	--------

PIN 8	0 V DC
-------	--------