

IMPACT20 PROFINET IO, DIGITAL IN-/OUTPUT MODULE

8 digital inputs and 8 digital outputs

Digital inputs/outputs


DI8 DO8 - 2 A

Connection cables are in the online shop under "Connection Technology".

Housing fully potted.

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

| | |
|-----------------------|---------------|
| ECLASS-6.0 | 27242604 |
| ECLASS-6.1 | 27242604 |
| ECLASS-7.0 | 27242604 |
| ECLASS-8.0 | 27242604 |
| ECLASS-9.0 | 27242604 |
| ECLASS-10.1 | 27242604 |
| ECLASS-11.1 | 27242604 |
| ECLASS-12.0 | 27242604 |
| ETIM-5.0 | EC001599 |
| customs tariff number | 85389099 |
| GTIN | 4048879047944 |
| Packaging unit | 1 |

Electrical data | Supply

| | |
|-------------------------|------------|
| Operating voltage DC | 24 V |
| Norm operating voltage | EN 61131-2 |
| Operating voltage US DC | 24 V |
| Total current max. | 8 A |
| Total current UA max. | 12 A |

Electrical data | Input

| | |
|--------------------|-----|
| Overload resistant | yes |
|--------------------|-----|

| | |
|---|--|
| Short-circuit protected | yes |
| Type input | PNP, for 3-wire sensors or mechanical switches |
| Current carrying capacity max. | 0,7 A |
| Electrical data Output | |
| Overload resistant | yes |
| Short-circuit protected | yes |
| Output current per pin max. | 2 A |
| Industrial communication Profinet | |
| PROFINET addressing | DCP |
| Diagnostics | |
| Diagnostic | No voltage, Under voltage |
| Diagnostic via BUS | per module and channel |
| Diagnostic via LED | per module and channel |
| Short circuit diagnosis | yes |
| LED display | Ethernet connection/data traffic |
| Overload diagnosis | yes |
| Installation | |
| Connection cross section max. | 2,5 mm ² |
| Device protection Electrical | |
| Degree of protection (EN IEC 60529) | IP20 |
| Mechanical data Mounting data | |
| Mounting method | geschnappt |
| Suitable for mounting type | mounting rail, (EN 60715) |
| Height | 117 mm |
| Width | 56 mm |
| Depth | 47 mm |
| Environmental characteristics Climatic | |
| Operating temperature min. | 0 °C |
| Operating temperature max. | 55 °C |
| Storage temperature min. | -20 °C |
| Storage temperature max. | 70 °C |
| Conformity | |
| Product standard | EN 61131-2 |
| Connection type 5 | |
| Connection type 1 | X0 |
| Connection type 2 | X1 |
| Connection type 3 | X2 |
| Connection type 4 | X3 |
| Connection | Spring clamp terminals FK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | colorless |
| No. of poles | 6 |
| PIN 1 | CH 00 |
| PIN 2 | CH 01 |
| PIN 3 | CH 02 |
| PIN 4 | CH 03 |
| PIN 5 | UI |
| PIN 6 | 0 V |
| Connection | Spring clamp terminals FK |
| Family construction form | terminal |

| | |
|--------------------------|---------------------------|
| Gender | female |
| Color contact carrier | colorless |
| No. of poles | 6 |
| PIN 1 | CH 10 |
| PIN 2 | CH 11 |
| PIN 3 | CH 12 |
| PIN 4 | CH 13 |
| PIN 5 | UA |
| PIN 6 | 0 V |
| Connection | Spring clamp terminals FK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | colorless |
| No. of poles | 6 |
| PIN 1 | CH 20 |
| PIN 2 | CH 21 |
| PIN 3 | CH 22 |
| PIN 4 | CH 23 |
| PIN 5 | US |
| PIN 6 | 0 V |
| Connection | Spring clamp terminals FK |
| Family construction form | terminal |
| Gender | female |
| Color contact carrier | colorless |
| No. of poles | 6 |
| PIN 1 | CH 30 |
| PIN 2 | CH 31 |
| PIN 3 | CH 32 |
| PIN 4 | CH 33 |
| PIN 5 | FE |
| PIN 6 | FE |
| Family construction form | RJ45 |
| Gender | female |
| Color contact carrier | black |
| No. of poles | 8 |
| PIN 1 | TX + |
| PIN 2 | TX - |
| PIN 3 | RX + |
| PIN 4 | n.c. |
| PIN 5 | n.c. |
| PIN 6 | RX - |
| PIN 7 | n.c. |
| PIN 8 | n.c. |