

CUBE20S POTENTIAL DISTRIBUTORS

8 x 0 V DC


Potential distributor
Expansion module
8x 0 V DC

[Link to Product](#)

Illustration



Product may differ from Image



| Commercial data | |
|-------------------------------------|---------------------------|
| ECLASS-6.0 | 27379201 |
| ECLASS-6.1 | 27242611 |
| ECLASS-7.0 | 27242611 |
| ECLASS-8.0 | 27242611 |
| ECLASS-9.0 | 27242611 |
| ECLASS-10.1 | 27242611 |
| ECLASS-11.1 | 27242611 |
| ECLASS-12.0 | 27242611 |
| ETIM-5.0 | EC001600 |
| customs tariff number | 85369010 |
| GTIN | 4048879422864 |
| Packaging unit | 1 |
| Electrical data Supply | |
| Operating voltage DC max. | 0 V |
| Total current max. | 10 A |
| Device protection Electrical | |
| Degree of protection (EN IEC 60529) | IP20 |
| Mechanical data Mounting data | |
| Mounting method | geschnappt |
| Suitable for mounting type | mounting rail, (EN 60715) |
| Height | 109 mm |

| | |
|-------|---------|
| Width | 12,9 mm |
| Depth | 52,5 mm |

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | 0 °C |
| Operating temperature max. | 60 °C |
| Storage temperature min. | -25 °C |
| Storage temperature max. | 70 °C |

Connection type 2

| | |
|--------------------------|---------------------------|
| Connection type 1 | Power |
| Connection type 2 | Power |
| Connection | Spring clamp terminals FK |
| Family construction form | terminal |
| Gender | female |
| No. of poles | 8 |
| PIN 1 | n.c. |
| PIN 2 | 24 V DC |
| PIN 3 | 0 V |
| PIN 4 | 24 V DC Sys |
| PIN 5 | n.c. |
| PIN 6 | 24 V DC |
| PIN 7 | 0 V |
| PIN 8 | 0 V Sys |
| Connection | Spring clamp terminals FK |
| Family construction form | terminal |
| Gender | female |
| No. of poles | 8 |
| PIN 1 | 0 V DC |
| PIN 2 | 0 V DC |
| PIN 3 | 0 V DC |
| PIN 4 | 0 V DC |
| PIN 5 | 0 V DC |
| PIN 6 | 0 V DC |
| PIN 7 | 0 V DC |
| PIN 8 | 0 V DC |