



Emergency-stop pushbutton with 2 positive opening contacts

in a IP65 enclosure


E-Stop 72P 2NC M12(5)  
with M12 connection  
5-pole  
Emergency-Stop button  
2 NC (positively-opening)  
with protection shroud

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371244
ECLASS-6.1	27371244
ECLASS-7.0	27371244
ECLASS-8.0	27371244

ECLASS-9.0	27371244
ECLASS-10.1	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ETIM-5.0	EC002034
customs tariff number	85365080
GTIN	4048879594691
Packaging unit	1

#### Electrical data | Output

Utilization category AC-15 (EN IEC 60947-5-1)	3 A @ 250 V
Utilization category DC-13 (EN IEC 60947-5-1)	2 A @ 24 V
Switching current (AC-15)	30 A
Switching current (DC-13)	2,2 A

#### Device protection

Condition lifetime	load-dependent, temperature dependent
--------------------	---------------------------------------

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	1000000 Cycles

#### Device protection | Mechanical

Mechanical endurance	1000000 Cycles
Operating life B10d	250000 Cycles

#### Mechanical data

Bounce time max.	9 ms
------------------	------

#### Mechanical data | Material data

Material contact	AgNi
------------------	------

#### Mechanical data | Mounting data

Mounting method	screwed
Height	104 mm
Width	72 mm
Depth	91 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C

#### Technical Data | Reliability

Lambda normally closed contact	20 %
--------------------------------	------

#### Connection type 1

Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	NC 1
PIN 2	NC 2
PIN 4	NC 1
PIN 5	NC 2