

## Emergency stop with 2 positive opening

contacts in a IP65 enclosure

E-Stop 42 2NC L M12(8)

with M12 connection

8-pole

Emergency-Stop button




2 NC (positively-opening)

LED-Ring can be lit

mounting with clip on the back side

### [Link to Product](#)

#### Illustration



Product may differ from Image



#### Commercial data

ECLASS-6.0	27371244
ECLASS-6.1	27371244
ECLASS-7.0	27371244

ECLASS-8.0	27371244
ECLASS-9.0	27371244
ECLASS-10.1	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ETIM-5.0	EC002034
customs tariff number	85365080
GTIN	4048879594219
Packaging unit	1

#### Electrical data

Operating voltage AC/DC LED illumination max.	30 V
Operating current LED illumination	4 mA @24 V DC

#### Electrical data | Supply

Operating voltage DC min.	1 V
Operating voltage DC max.	36 V
Operating voltage DC (UL Recognized)	30 V
Operating current	1,5 A

#### Device protection

Condition lifetime	load-dependent, temperature dependent
--------------------	---------------------------------------

#### Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	50000 Cycles

#### Device protection | Mechanical

Mechanical endurance	50000 Cycles
Operating life B10d	250000 Cycles

#### Mechanical data

Bounce time max.	10 ms
------------------	-------

#### Mechanical data | Material data

Material contact	AgNi
------------------	------

#### Mechanical data | Mounting data

Height	52 mm
Width	124 mm
Depth	42 mm

#### Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C

#### Technical Data | Reliability

Lambda normally closed contact	20 %
--------------------------------	------

#### Connection type 1

Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	8
PIN 1	NC 1
PIN 2	NC 1 +
PIN 3	NC 2

PIN 4	NC 2 +
PIN 7	X 2 -
PIN 8	X 1 +