

LED-INDICATOR OPAC / GREEN

LED-230VAC IP65


(green)  
230 V AC  
The modules are suitable for wall thickness of 1.5...5.0 mm.

Link to Product

Illustration



Product may differ from Image



Commercial data

ECLASS-6.0	27261590
ECLASS-6.1	27261501
ECLASS-7.0	27261501
ECLASS-8.0	27261501
ECLASS-9.0	27261501
ECLASS-10.1	27261501
ECLASS-11.1	27261501
ECLASS-12.0	27261501
ETIM-5.0	EC000272
customs tariff number	85318070
GTIN	4048879041256
Packaging unit	10

Electrical data | Supply

Operating voltage AC	230 V
Operating voltage AC min.	207 V
Operating voltage AC max.	253 V
Current consumption min.	8 mA
Current consumption max.	12 mA

Installation | Connection

Connection information	Faston 2.8×0.8 mm
------------------------	-------------------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data

Diameter LED 5 mm

**Mechanical data | Material data**

Material housing Plastic

**Mechanical data | Mounting data**

Diameter front panel drilling 9 mm

**Environmental characteristics | Climatic**

Operating temperature min. -20 °C

Operating temperature max. 50 °C