

MTS 1-PHASE CONTROL AND ISOLATION TRANSFORMER

P: 100VA IN: 208...550VAC OUT: 24VAC

Single-phase - Control and Isolation Transformers  
100 VA  
Isolation class T 40/B  
Other voltages on request.

[Link to Product](#)

Illustration



Product may differ from Image



| Commercial data |          |
|-----------------|----------|
| ECLASS-6.0      | 27031302 |
| ECLASS-6.1      | 27031302 |
| ECLASS-7.0      | 27031302 |
| ECLASS-8.0      | 27031302 |
| ECLASS-9.0      | 27031302 |
| ECLASS-10.1     | 27031302 |

|                       |               |
|-----------------------|---------------|
| ECLASS-11.1           | 27031302      |
| ECLASS-12.0           | 27031302      |
| ETIM-5.0              | EC002486      |
| customs tariff number | 85043180      |
| GTIN                  | 4048879372367 |
| Packaging unit        | 1             |

**Electrical data | Supply**

|                 |              |
|-----------------|--------------|
| Power frequency | 50 ... 60 Hz |
|-----------------|--------------|

**Electrical data | Input**

|                                          |                                                       |
|------------------------------------------|-------------------------------------------------------|
| Input voltage 1 AC                       | 208 V                                                 |
| Input voltage 2 AC                       | 550 V                                                 |
| Input voltage AC                         | 208, 230, 380, 400, 420, 440, 460, 480, 500, 525, 550 |
| Input current at input voltage 1 AC      | 0,57 A                                                |
| Input current at input voltage 2 AC      | 0,21 A                                                |
| Inrush current at input voltage 1        | 9,7 A                                                 |
| Inrush current at input voltage 2        | 3,7 A                                                 |
| Short-circuit current at input voltage 1 | 7,6 A                                                 |
| Short-circuit current at input voltage 2 | 2,9 A                                                 |

**Electrical data | Output**

|                           |        |
|---------------------------|--------|
| Output voltage AC         | 24 V   |
| Output voltage adjustable | no     |
| Power rating AC max.      | 100 VA |

**Device protection | Electrical**

|                                        |        |
|----------------------------------------|--------|
| Insulation test voltage input - output | 6,3 kV |
|----------------------------------------|--------|

**Mechanical data | Mounting data**

|                            |                         |
|----------------------------|-------------------------|
| Suitable for mounting type | Schlüssellochaufhängung |
| Mounting dimension a       | 64,5 mm                 |
| Mounting dimension b       | 64 mm                   |
| Mounting dimension c       | 4,8 mm                  |
| Height                     | 88 mm                   |
| Width                      | 84 mm                   |
| Depth                      | 93 mm                   |
| Diameter bore              | 4,8 mm                  |
| Length bore                | 8,4 mm                  |

**Environmental characteristics | Climatic**

|                            |        |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 40 °C  |
| Storage temperature min.   | -40 °C |
| Storage temperature max.   | 80 °C  |

**Conformity**

|                  |                                                 |
|------------------|-------------------------------------------------|
| Product standard | EN 61558-2-4, EN 61558-2-6, EN 62041 category 0 |
|------------------|-------------------------------------------------|

**Connection type 3**

|                          |                    |
|--------------------------|--------------------|
| Connection type 1        | Input              |
| Connection type 2        | Output             |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| No. of poles             | 8                  |
| PIN 1                    | 1                  |
| PIN 2                    | 2                  |
| PIN 3                    | 3                  |

|                          |                    |
|--------------------------|--------------------|
| PIN 4                    | 4                  |
| PIN 5                    | 5                  |
| PIN 6                    | 6                  |
| PIN 7                    | 7                  |
| PIN 8                    | 8                  |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| No. of poles             | 2                  |
| PIN 1                    | 9                  |
| PIN 2                    | 10                 |
| Connection               | Screw terminals SK |
| Family construction form | terminal           |
| Gender                   | female             |
| Color contact carrier    | metallic           |
| No. of poles             | 1                  |
| PIN 1                    | PE                 |