



MTS SINGLE-PHASE CONTROL AND ISOLATION TRANSFORMER

P:150VA IN:400VAC±5% OUT:24VAC/230VAC

Single-phase - Control and Isolation Transformers
150 VA
Isolation class T 40/B

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27031202
ECLASS-6.1	27031302
ECLASS-7.0	27031302
ECLASS-8.0	27031302
ECLASS-9.0	27031302
ECLASS-10.1	27031302

ECLASS-11.1	27031302
ECLASS-12.0	27031302
ETIM-5.0	EC002485
customs tariff number	85043180
GTIN	4048879307154
Packaging unit	1
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	
Input voltage AC	400 V
Input voltage AC min.	380 V
Input voltage AC max.	420 V
Current input AC	0,45 A
Max. inrush current	4,5 A
Short-circuit current	6 A
Electrical data Output	
Output voltage AC 1	24 V
Output voltage AC 2	230 V
Output voltage adjustable	no
Power rating AC max.	150 VA
Device protection Electrical	
Insulation test voltage input - output	5,8 kV
Mechanical data Mounting data	
Mounting method	screwed
Mounting dimension a	64,5 mm
Mounting dimension b	64 mm
Mounting dimension c	4,8 mm
Height	88 mm
Width	84 mm
Depth	98 mm
Diameter bore	4,8 mm
Length bore	8,4 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	40 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Conformity	
Product standard	EN 61558-2-4, EN 61558-2-6, EN 62041 category 0
Connection type 3	
Connection type 1	Input
Connection type 2	Output
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 1	+ 5%
PIN 3	- 5%
PIN 4	400 V
Connection	Screw terminals SK
Family construction form	terminal

Gender	female
No. of poles	4
PIN 2	24 V DC
PIN 4	230 V
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	metallic
No. of poles	1
PIN 1	PE