



MST SINGLE-PHASE SAFETY TRANSFORMER

P:160VA IN:230VAC OUT:20VAC

Single-phase - Control and Isolation Transformers
160 VA
Isolation class T 40/B
Other voltages on request.

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27031202
ECLASS-6.1	27031302
ECLASS-7.0	27031302
ECLASS-8.0	27031302
ECLASS-9.0	27031302
ECLASS-10.1	27031302

ECLASS-11.1	27031302
ECLASS-12.0	27031302
ETIM-5.0	EC002485
customs tariff number	85043180
GTIN	4048879318075
Packaging unit	1

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage 1 AC	230 V
Input voltage AC	230 V
Current input AC	0,81 A
Max. inrush current	6,6 A
Short-circuit current	11,5 A

Electrical data | Output

Output voltage AC	20 V
Output voltage adjustable	no
Power rating AC max.	160 VA

Device protection | Electrical

Insulation test voltage input - output	3,8 kV
--	--------

Mechanical data | Mounting data

Suitable for mounting type	Schlüssellochaufhängung
Mounting dimension a	75,3 mm
Mounting dimension b	84 mm
Mounting dimension c	5,8 mm
Height	91 mm
Width	97 mm
Depth	105 mm
Diameter bore	5,8 mm
Length bore	12 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	40 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C

Conformity

Product standard	EN 61558-2-6, EN 62041 category 0
------------------	-----------------------------------

Connection type 3

Connection type 1	Input
Connection type 2	Output
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 2	230 V
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 2	20 V
Connection	Screw terminals SK

Family construction form	terminal
Gender	female
Color contact carrier	metallic
No. of poles	1
PIN 1	PE