



MIRO SAFE+ SWITCH ECOA 24

24 VAC/DC - 2 N/O contact /1 PLC output

- 4 A
- Protection-door and emergency-stop control
- Light curtain control
- Safety magnetic switch control
- Automatic/manual reset/start

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371819
ECLASS-6.1	27371819
ECLASS-7.0	27371819
ECLASS-8.0	27371819
ECLASS-9.0	27371819

ECLASS-10.1	27371819
ECLASS-11.1	27371819
ECLASS-12.0	27371819
ETIM-5.0	EC001449
customs tariff number	85364900
GTIN	4048879367561
Packaging unit	1
Safety codes	
Category (EN ISO 13849-1)	4
Electrical data Supply	
Power consumption max.	2 W
Apparent power max.	5,2 VA
Electrical data Input	
Input voltage AC	24 V
Input voltage AC min.	20,4 V
Input voltage AC max.	26,4 V
Input voltage DC	24 V
Input voltage DC min.	20,4 V
Input voltage DC max.	28,8 V
Electrical data Output	
No. of auxiliary contacts	0
No. of alarm outputs	1
No. of safety contacts	2
Utilization category AC-15 (EN IEC 60947-5-1)	2 A @ 230 V
Utilization category DC-13 STOP0 (EN IEC 60947-5-1)	1 A @ 24 V
Alarm outputs	Y1
Switching voltage AC max.	250 V
Switching voltage DC max.	250 V
Switching current max.	4 A
Switching capacity signal output Y1	100 mA @ 24 V DC
Switching capacity safety contacts STOP0	max. 250 V AC/4 A; min. 5 V AC/1 mA (resist./ind.), at suitable suppression
Safety contacts	13-14, 23-24
Device protection	
Condition lifetime	load-dependent
Device protection Electrical	
Electrical lifetime	10000000 Cycles
Device protection Mechanical	
Mechanical endurance	10000000 Cycles
Mechanical data Material data	
Material contact	Ag Sn O
Material properties contact	positively driven, self-cleaning
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	100 mm
Width	22,5 mm
Depth	121 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	60 °C

Storage temperature min.	-40 °C
--------------------------	--------

Storage temperature max.	85 °C
--------------------------	-------

Connection type 4

Connection	Spring clamp terminals FK
------------	---------------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

No. of poles	4
--------------	---

PIN 1	X 2
-------	-----

PIN 2	S 22
-------	------

PIN 3	S 12
-------	------

PIN 4	A 2
-------	-----

Connection	Spring clamp terminals FK
------------	---------------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

No. of poles	4
--------------	---

PIN 1	X 1
-------	-----

PIN 2	Y 1
-------	-----

PIN 3	S 11
-------	------

PIN 4	A 1
-------	-----

Connection	Spring clamp terminals FK
------------	---------------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

No. of poles	4
--------------	---

PIN 1	13
-------	----

PIN 2	14
-------	----

PIN 3	23
-------	----

PIN 4	24
-------	----

Connection	Spring clamp terminals FK
------------	---------------------------

Family construction form	terminal
--------------------------	----------

Gender	female
--------	--------

Color contact carrier	black
-----------------------	-------

No. of poles	4
--------------	---