

**MODLINK MSDD DATA INSERT**

1×SUB-D25 fem./male + 1×SUB-D9 fem./male + 1×RJ45

RJ45; SUB-D9; SUB-D25  
1× RJ45, 8-pole metal, CAT5e (female/female)  
1× SUB-D9 (female/male)  
1× SUB-D25 (female/male)

**Link to Product**

**Illustration**



Product may differ from Image



**Commercial data**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
customs tariff number	85366990
GTIN	4048879037402
Packaging unit	1

**Mechanical data | Mounting data**

Height	88 mm
Width	51 mm
Depth	21 mm

**Environmental characteristics | Climatic**

Storage temperature min.	5 °C
Storage temperature max.	40 °C

**Shielding plate**

Connection information	Threaded hole M4
Tightening torque	0,9 Nm
<b>SUB-D9</b>	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D9
Family type Back side	SUB-D9
Gender	female
Gender Rear	male
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	9
<b>SUB-D25</b>	
Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	3 A
Current operating max. (UL)	175 mA
Family construction form	SUB-D25
Family type Back side	SUB-D25
Gender	female
Gender Rear	male
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
No. of poles	25
<b>RJ45</b>	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector