

**MODLINK MSDD DATA INSERT**

1×SUB-D9 fem./male + 1×RJ45 + 1×BNC female/female

- BNC; RJ45; SUB-D9  
1 × BNC (female/female)  
1 × RJ45, 8-pole metal, CAT5e (female/female)  
1 × SUB-D9 (female/male)

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27189217      |
| ECLASS-6.1            | 27189217      |
| ECLASS-7.0            | 27189217      |
| ECLASS-8.0            | 27189217      |
| ECLASS-9.0            | 27182806      |
| ECLASS-10.1           | 27182806      |
| ECLASS-11.1           | 27182806      |
| ECLASS-12.0           | 27182806      |
| ETIM-5.0              | EC002625      |
| customs tariff number | 85366990      |
| GTIN                  | 4048879037396 |
| Packaging unit        | 1             |

Mechanical data | Mounting data

|        |       |
|--------|-------|
| Height | 88 mm |
| Width  | 51 mm |
| Depth  | 33 mm |

Environmental characteristics | Climatic

|                          |       |
|--------------------------|-------|
| Storage temperature min. | 5 °C  |
| Storage temperature max. | 40 °C |

SUB-D9

|                                       |  |
|---------------------------------------|--|
| Operating voltage AC                  | 48 V   |
| Operating voltage DC                  | 48 V   |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42,4 V   |
| Operating current                     | 3 A  |
| Current operating max. (UL)           | 175 mA   |
| Family construction form              | SUB-D9   |
| Family type Back side                 | SUB-D9   |
| Gender                                | female   |
| Gender Rear                           | male   |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 9  |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |

**BNC**

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | BNC               |
| Gender                                | female            |
| Looking techniques                    | Snap-in connector |
| No. of poles                          | 2 + PE            |
| Protection contact present            | yes               |