

MODLINK MSDD DATA INSERT

1×SUB-D9 female/female + 1×RJ45 + 1×RJ12 + 1×USB-A

- RJ45; RJ12; USB; USB (A); SUB-D9
- 1× RJ45, 8-pole metal, CAT5e (female/female)
- 1× RJ12 (6-pole plastic)
- 1× USB 2.0 (female/female) form A
- 1× SUB-D9 (female/female)

Link to Product

Illustration



Product may differ from Image



| Commercial data                          |               |
|--|---------------|
| ECLASS-6.0                               | 27189217      |
| ECLASS-6.1                               | 27189217      |
| ECLASS-7.0                               | 27189217      |
| ECLASS-8.0                               | 27189217      |
| ECLASS-9.0                               | 27189217      |
| ECLASS-10.1                              | 27182806      |
| ECLASS-11.1                              | 27182806      |
| ECLASS-12.0                              | 27182806      |
| ETIM-5.0                                 | EC002625      |
| customs tariff number                    | 85366990      |
| GTIN                                     | 4048879310116 |
| Packaging unit                           | 1             |
| Mechanical data   Mounting data          |               |
| Height                                   | 88 mm         |
| Width                                    | 51 mm         |
| Depth                                    | 45 mm         |
| Environmental characteristics   Climatic |               |
| Storage temperature min.                 | 5 °C          |
| Storage temperature max.                 | 40 °C         |

|                                       |  |
|---------------------------------------|--|
| <b>Shielding plate</b>                |  |
| Connection information                | Threaded hole M4                               |
| Tightening torque                     | 0,9 Nm   |
| <b>USB</b>                            |  |
| Operating voltage AC                  | 48 V   |
| Operating voltage DC                  | 48 V   |
| Operating voltage DC (UL-listed)      | 42,4 V   |
| Operating current max.                | 500 mA   |
| USB specification                     | 2.0  |
| Data transmission rate max.           | 480 MBit/s                                     |
| Looking techniques                    | Snap-in connector                              |
| <b>SUB-D9</b>                         |  |
| Operating voltage AC                  | 48 V   |
| Operating voltage DC                  | 48 V   |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42,4 V   |
| Operating current                     | 3 A  |
| Current operating max. (UL)           | 175 mA   |
| Family construction form              | SUB-D9   |
| Family type Back side                 | SUB-D9   |
| Gender                                | female   |
| Gender Rear                           | female   |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 9  |
| <b>RJ12</b>                           |  |
| Operating voltage AC max.             | 48 V   |
| Operating voltage DC max.             | 48 V   |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42,4 V   |
| Operating current max.                | 1 A  |
| Current operating max. (UL)           | 175 mA   |
| Family construction form              | RJ12   |
| Family type Back side                 | RJ12   |
| Looking techniques                    | Snap-in connector                              |
| <b>RJ45</b>                           |  |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42,4 V   |
| Current operating max. (UL)           | 175 mA   |
| Family construction form              | RJ45   |
| Family type Back side                 | RJ45   |
| Cable category min.                   | Cat5e  |
| Looking techniques                    | Snap-in connector                              |