

**Modlink MSDD-set: Frame 4000-68123-0000000,**  
 insert 4000-68000-1100000 + 4000-68000-0010000

## [Link to Product](#)

### Illustration



Product may differ from Image

**Commercial data**

|                       |               |
|-----------------------|---------------|
| ECLASS-6.0            | 27189217      |
| ECLASS-7.0            | 27189217      |
| ECLASS-8.0            | 27189217      |
| ECLASS-9.0            | 27189217      |
| ETIM-5.0              | EC002625      |
| customs tariff number | 85389099      |
| GTIN                  | 4048879034074 |
| Packaging unit        | 1             |

**Frame**

|   |                       |
|---|-----------------------|
| Degree of protection (EN IEC 60529)           | IP65                  |
| Operating temperature min.                    | -10 °C                |
| Operating temperature max.                    | 60 °C                 |
| Storage temperature min.                      | -25 °C                |
| Storage temperature max.                      | 60 °C                 |
| Suitable for installation wall thickness min. | 1 mm                  |
| Suitable for installation wall thickness max. | 5 mm                  |
| Coating housing                               | surface finished      |
| Material housing                              | Fine zinc die casting |

**Germany (VDE)**

|                               |                    |
|-------------------------------|--------------------|
| Connection cross section max. | 6 mm <sup>2</sup>  |
| AWG number max.               | 10                 |
| Operating voltage AC          | 250 V              |
| Operating current             | 16 A               |
| Status indication LED         | yellow             |
| Connection                    | Screw terminals SK |
| No. of poles                  | 2 + PE             |
| Connections per pole          | 2                  |
| Protection contact present    | yes                |

**SUB-D25**

|                                       |  |
|---------------------------------------|--|
| Operating voltage AC                  | 48 V   |
| Operating voltage DC                  | 48 V   |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42,4 V   |
| Operating current                     | 3 A  |
| Current operating max. (UL)           | 175 mA   |
| Family construction form              | SUB-D25  |
| Family type Back side                 | SUB-D25  |
| Gender                                | female   |
| Gender Rear                           | male   |
| Looking techniques                    | Standard UNC 4-40 screw thread bolt (EN 60807) |
| No. of poles                          | 25   |

**RJ12**

|                                       |        |
|---------------------------------------|--------|
| Operating voltage AC max.             | 48 V   |
| Operating voltage DC max.             | 48 V   |
| Operating voltage AC max. (UL-listed) | 30 V   |
| Operating voltage DC max. (UL-listed) | 42,4 V |

|                             |                   |
|-----------------------------|-------------------|
| Operating current max.      | 1 A               |
| Current operating max. (UL) | 175 mA            |
| Family construction form    | RJ12              |
| Family type Back side       | RJ12              |
| Looking techniques          | Snap-in connector |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |