

PROPORTIONAL AMPLIFIER, SNAP-ON



Startup time 1 second

Control electronics for proportional valves
18...32 V DC, smoothed (2200 µF/1 A)
Screw terminals
Start-up: 1 s

The amplifier regulates the current supply to a proportional valve. This current is proportional to the set-point on the amplifier's input. A voltage output of 10 V is available for set-point adjustment. Zero point, current, and ramp time can be set with the potentiometer. In connection with a proportional valve, a pressure or a quantity can be set in a continuously adjustable way.

Link to Product

Illustration



Product may differ from Image

Electrical data Supply	
Operating voltage DC min.	18 V
Operating voltage DC max.	32 V
Operating current max.	2,5 A
Current consumption max.	50 mA
Electrical data Input	
Resistance input min.	200 kΩ

Control voltage DC min.	0 V
-------------------------	-----

Control voltage DC max.	10 V
-------------------------	------

Electrical data | Output

Output voltage DC	24 V
-------------------	------

Output voltage adjustable	no
---------------------------	----

Output current	2,5 A
----------------	-------

Diagnostics

Status indication LED	green
-----------------------	-------

Installation | Connection

Connection	Screw terminals SK
------------	--------------------

Device protection | Electrical

Short-circuit protection output	yes
---------------------------------	-----

Overtemperature protection output	yes
-----------------------------------	-----

Mechanical data | Mounting data

Mounting method	geschnappt
-----------------	------------

Suitable for mounting type	mounting rail, (EN 60715)
----------------------------	---------------------------

Height	75 mm
--------	-------

Width	22,5 mm
-------	---------

Depth	102 mm
-------	--------

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Commercial data

customs tariff number	85437090
-----------------------	----------

GTIN	4048879364911
------	---------------

Packaging unit	1
----------------	---