

**Adaptor M12 male / M12 female A-cod. shielded**

4-pol., U-I CONVERTER




Adapter


Male - female

M12 – M12, 4-pole

shielded

Voltage/current converter

[Link to Product](#)**Illustration**



Product may differ from Image



General product information	
Application	Voltage/current converter
Commercial data	
ECLASS-6.0	27143423
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-8.0	27440102
ECLASS-9.0	27440106
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440106
ETIM-5.0	EC001855
customs tariff number	85366990
GTIN	4048879143172
Packaging unit	1
Electrical data   Supply	
Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	30 V
Current operating per contact max.	4 A
Installation   Connection	
Tightening torque	0,6 Nm
Mounting set	M12 x 1
Device protection   Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	screwed, mounted
Rated insulation voltage	800 V
Mechanical data   Material data	
Coating locking	Nickel
Material housing	PUR
Locking material	Zinc die-casting

Mounting method	inserted, screwed, Shaking protection
-----------------	---------------------------------------

### Environmental characteristics | Climatic

Operating temperature min. -25 °C

Operating temperature max.	85 °C
----------------------------	-------