




PVC 3x0.75 bk 40m

The resistance to aggressive media should be individually tested for your application. Further details on request.

### Illustration



|                   |        |
|-------------------|--------|
| Cable length      | 40 m   |
| <b>Side 1</b>     |        |
| Tightening torque | 0,4 Nm |

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | [shop@murrinc.com](mailto:shop@murrinc.com) | [shop.murrinc.com](http://shop.murrinc.com)

Thread M2.5

| Commercial data                          |                                                                                                                                                       |
|------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| ECLASS-6.0                               | 27279218                                                                                                                                              |
| ECLASS-7.0                               | 27279218                                                                                                                                              |
| ECLASS-8.0                               | 27279218                                                                                                                                              |
| ECLASS-9.0                               | 27060311                                                                                                                                              |
| ECLASS-10.1                              | 27060312                                                                                                                                              |
| ECLASS-11.1                              | 27060312                                                                                                                                              |
| ECLASS-12.0                              | 27060312                                                                                                                                              |
| ETIM-5.0                                 | EC001855                                                                                                                                              |
| customs tariff number                    | 85444290                                                                                                                                              |
| GTIN                                     | 4048879133470                                                                                                                                         |
| Packaging unit                           | 1                                                                                                                                                     |
| Electrical data                          |                                                                                                                                                       |
| Drop-out delay time max.                 | 20 ms                                                                                                                                                 |
| Electrical data   Supply                 |                                                                                                                                                       |
| Operating voltage AC                     | 24 V                                                                                                                                                  |
| Operating voltage AC min.                | 19,2 V                                                                                                                                                |
| Operating voltage AC max.                | 28,8 V                                                                                                                                                |
| Operating voltage DC                     | 24 V                                                                                                                                                  |
| Operating voltage DC min.                | 18 V                                                                                                                                                  |
| Operating voltage DC max.                | 30 V                                                                                                                                                  |
| Cut-off peak voltage max.                | 55 V                                                                                                                                                  |
| Current operating per contact max.       | 4 A                                                                                                                                                   |
| Device protection   Electrical           |                                                                                                                                                       |
| Degree of protection (EN IEC 60529)      | IP67                                                                                                                                                  |
| Additional condition protection degree   | inserted, screwed                                                                                                                                     |
| Mechanical data   Material data          |                                                                                                                                                       |
| Color housing                            | black                                                                                                                                                 |
| Material housing                         | Plastic                                                                                                                                               |
| Mechanical data   Mounting data          |                                                                                                                                                       |
| Mounting method                          | inserted, screwing                                                                                                                                    |
| Environmental characteristics   Climatic |                                                                                                                                                       |
| Operating temperature min.               | -25 °C                                                                                                                                                |
| Operating temperature max.               | 85 °C                                                                                                                                                 |
| Additional condition temperature range   | depending on cable quality                                                                                                                            |
| Important installation notes             |                                                                                                                                                       |
| Note on strain relief                    | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                   | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| Installation   Cable                     |                                                                                                                                                       |
| wire arrangement                         | black 1, black 2, green-yellow                                                                                                                        |
| Cable identification                     | 616                                                                                                                                                   |
| Cable Type                               | 1                                                                                                                                                     |
| Printing color of wire insulation        | white (isolation black)                                                                                                                               |
| Jacket Color                             | black                                                                                                                                                 |
| Amount stranding                         | 1                                                                                                                                                     |
| Stranding                                | 3 wires twisted                                                                                                                                       |
| wire arrangement                         | black 1, black 2, green-yellow                                                                                                                        |
| Cable weight                             | 61,6 g/m                                                                                                                                              |
| Material jacket                          | PVC                                                                                                                                                   |

|                                                   |                                                      |
|---------------------------------------------------|------------------------------------------------------|
| Shore hardness jacket                             | 80 ± 5 Shore A                                       |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, silicone-free     |
| Outer-diameter (jacket)                           | 5,9 mm                                               |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                |
| Material wire insulation                          | PVC                                                  |
| Amount wires                                      | 3                                                    |
| Outer diameter insulation                         | 1,8 mm                                               |
| Outer diameter tolerance core insulation          | ± 5 %                                                |
| Shore hardness wire insulation                    | 43 ± 5 Shore D                                       |
| Material properties wire insulation               | good machinability                                   |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, silicone-free     |
| Printing color of wire insulation                 | white (isolation black)                              |
| Amount strands (wire)                             | 24                                                   |
| Diameter of single wires                          | 0,2 mm                                               |
| Conductor crosssection (wire)                     | 0,75 mm <sup>2</sup>                                 |
| Material conductor wire                           | Stranded copper wire, bare                           |
| Conductor type (wire)                             | Strand class 5                                       |
| Max. rated voltage (conductor - conductor)        | 500 V                                                |
| Max. rated voltage (conductor - ground)           | 300 V                                                |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                    |
| Current load capacity min. wire                   | 12 A                                                 |
| Electrical resistance line constant wire          | 26 Ω/km @ 20 °C                                      |
| AC withstand voltage (wire - wire)                | 3 kV @ 60 s                                          |
| Power frequency withstand voltage (wire - jacket) | 3 kV @ 60 s                                          |
| Min. operating temperature (static)               | -30 °C                                               |
| Max. operating temperature (fixed)                | 70 °C                                                |
| Operating temperature min. (dynamic)              | -5 °C                                                |
| Operating temperature max. (dynamic)              | 70 °C                                                |
| UV resistance                                     | DIN EN ISO 4892-2 A                                  |
| Flame resistance                                  | UL 1581 § 1100 FT2   IEC 60332-2-2   UL 1581 § 1090  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404 |
| Bending radius (fixed)                            | 5 x Outer diameter                                   |
| Bending radius (dynamic)                          | 10 x Outer diameter                                  |