



M12 Xtreme male 90° A-cod. / valve plug MDC06-2s

PUR 2x0.75 bk UL/CSA+drag ch. 1.5m


Xtreme - Outdoor  
Further cable lengths on request.  
Male 90° – male straight  
M12  
4-pole  
Deutsch MDC06-2S  
2-pole  
Art-No. 7005 - M12 Lite - (plastic hexagonal screw) on request  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image



|                                           |       |
|-------------------------------------------|-------|
| Cable length                              | 1,5 m |
| Side 1                                    |       |
| Family construction form                  | M12   |
| suitable for corrugated tube (internal Ø) | 10 mm |

|                                                 |                                                                                                                                                       |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Coding                                          | A                                                                                                                                                     |
| Material                                        | PUR                                                                                                                                                   |
| Width across flats                              | SW14                                                                                                                                                  |
| <b>Side 2</b>                                   |                                                                                                                                                       |
| Tightening torque                               | 0,6 Nm                                                                                                                                                |
| Family construction form                        | Amphenol AT06-2S                                                                                                                                      |
| Thread                                          | M12 x 1                                                                                                                                               |
| suitable for corrugated tube (internal Ø)       | 11 mm                                                                                                                                                 |
| Material                                        | PA                                                                                                                                                    |
| <b>Commercial data</b>                          |                                                                                                                                                       |
| ECLASS-6.0                                      | 27279218                                                                                                                                              |
| ECLASS-7.0                                      | 27279218                                                                                                                                              |
| ECLASS-8.0                                      | 27279218                                                                                                                                              |
| ECLASS-9.0                                      | 27060311                                                                                                                                              |
| ECLASS-10.1                                     | 27060312                                                                                                                                              |
| ECLASS-11.1                                     | 27060312                                                                                                                                              |
| ECLASS-12.0                                     | 27060312                                                                                                                                              |
| ETIM-5.0                                        | EC001855                                                                                                                                              |
| customs tariff number                           | 85444290                                                                                                                                              |
| GTIN                                            | 4048879657747                                                                                                                                         |
| Packaging unit                                  | 1                                                                                                                                                     |
| <b>Electrical data   Supply</b>                 |                                                                                                                                                       |
| Operating voltage AC min.                       | 12 V                                                                                                                                                  |
| Operating voltage AC max.                       | 230 V                                                                                                                                                 |
| Operating voltage DC min.                       | 12 V                                                                                                                                                  |
| Operating voltage DC max.                       | 230 V                                                                                                                                                 |
| Current operating per contact max.              | 4 A                                                                                                                                                   |
| <b>Device protection   Electrical</b>           |                                                                                                                                                       |
| Degree of protection (EN IEC 60529)             | IP65, IP67, IP68, IP66K                                                                                                                               |
| Additional condition protection degree          | inserted, screwed                                                                                                                                     |
| Pollution Degree                                | 3                                                                                                                                                     |
| Rated surge voltage                             | 2,5 kV                                                                                                                                                |
| Material group (IEC 60664-1)                    | I                                                                                                                                                     |
| Additional suppressor                           | without components                                                                                                                                    |
| <b>Mechanical data   Material data</b>          |                                                                                                                                                       |
| Material gasket                                 | Silicon                                                                                                                                               |
| Locking material                                | Stainless steel 1.4305 (V2A)                                                                                                                          |
| <b>Mechanical data   Mounting data</b>          |                                                                                                                                                       |
| Mounting method                                 | inserted, screwed, Shaking protection                                                                                                                 |
| Looking techniques                              | Snap-in connector                                                                                                                                     |
| <b>Environmental characteristics   Climatic</b> |                                                                                                                                                       |
| Operating temperature min.                      | -25 °C                                                                                                                                                |
| Operating temperature max.                      | 85 °C                                                                                                                                                 |
| Additional condition temperature range          | depending on cable quality                                                                                                                            |
| <b>Important installation notes</b>             |                                                                                                                                                       |
| Note on strain relief                           | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.                                                   |
| Note on bending radius                          | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |
| <b>Installation   Cable</b>                     |                                                                                                                                                       |
| Cable identification                            | 754                                                                                                                                                   |
| Cable Type                                      | 3                                                                                                                                                     |

|                                                   |                                                                |
|---------------------------------------------------|----------------------------------------------------------------|
| Jacket Color                                      | black                                                          |
| Type of Certificate                               | cURus                                                          |
| Amount stranding                                  | 1                                                              |
| Stranding                                         | 2 wires twisted                                                |
| wire arrangement                                  | brown, blue                                                    |
| Cable weight                                      | 40,7 g/m                                                       |
| Material jacket                                   | PUR                                                            |
| Shore hardness jacket                             | 90 ± 5 Shore A                                                 |
| Freedom from ingredients (jacket)                 | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Outer-diameter (jacket)                           | 5 mm                                                           |
| Tolerance outer diameter (sheath)                 | ± 5 %                                                          |
| Material wire insulation                          | PP                                                             |
| Amount wires                                      | 2                                                              |
| Outer diameter insulation                         | 1,7 mm                                                         |
| Outer diameter tolerance core insulation          | ± 5 %                                                          |
| Shore hardness wire insulation                    | 70 ± 5 Shore D                                                 |
| Ingredient freeness wire insulation               | lead-free, cadmium-free, CFC-free, halogen-free, silicone-free |
| Amount strands (wire)                             | 42                                                             |
| Diameter of single wires                          | 0,15 mm                                                        |
| Conductor crosssection (wire)                     | 0,75 mm²                                                       |
| Material conductor wire                           | Stranded copper wire, bare                                     |
| Conductor type (wire)                             | strand class 6                                                 |
| Traversing distance (C-track)                     | 10 m @ 25 °C   horizontal                                      |
| Nominal voltage AC max.                           | 300 V                                                          |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                              |
| Current load capacity min. wire                   | 12 A                                                           |
| Electrical resistance line constant wire          | 26 Ω/km @ 20 °C                                                |
| AC withstand voltage (wire - wire)                | 2,5 kV @ 60 s                                                  |
| Power frequency withstand voltage (wire - jacket) | 2,5 kV @ 60 s                                                  |
| Min. operating temperature (static)               | -40 °C                                                         |
| Max. operating temperature (fixed)                | 80 °C / 90 °C @ 10000 h Operation                              |
| Operating temperature min. (dynamic)              | -25 °C                                                         |
| Operating temperature max. (dynamic)              | 80 °C / 90 °C @ 10000 h Operation                              |
| UV resistance                                     | DIN EN ISO 4892-2 A                                            |
| Flame resistance                                  | UL 1581 § 1090   UL 1581 § 1100 FT2   IEC 60332-2-2            |
| chemical resistance                               | Good, application-related testing                              |
| Gasoline resistance                               | Good, application-related testing                              |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing           |
| Bending radius (fixed)                            | 5 x Outer diameter                                             |
| Bending radius (dynamic)                          | 10 x Outer diameter                                            |
| Travel speed (C-track)                            | 10 Mio. @ 25 °C                                                |
| No. of torsion cycles                             | 2 Mio.                                                         |
| Torsion stress                                    | ± 180 °/m                                                      |
| Torsion speed                                     | 35 cycles/min                                                  |