

Male module, 5-pole, Push-in

400 V, 16 A


Male
5-pole
Push-In terminals
Technical data will be only guaranteed with Murrelektronik components.
Please use wire end ferrule.
The clip 70MH-ZZ100-0000000 is needed (2×)

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27143424
ECLASS-6.1	27261204
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440217
ECLASS-10.1	27440217
ECLASS-11.1	27440217
ECLASS-12.0	27440217
ETIM-5.0	EC000438
customs tariff number	85366990
GTIN	4048879664004
Packaging unit	5
Electrical data Supply	
Operating voltage AC	400 V
Operating voltage DC	400 V
Operating current	16 A
Installation	
Connection cross section min.	0,14 mm²

Connection cross section max.	2,5 mm ²
-------------------------------	---------------------

AWG number min.	26
-----------------	----

AWG number max.	14
-----------------	----

Installation | Connection

Connection	Push-In spring clamp terminals
------------	--------------------------------

Gender	male
--------	------

Mating cycles min.	500
--------------------	-----

Installation | Pin assignment

No. of poles	5
--------------	---

Device protection | Electrical

Pollution Degree	3
------------------	---

Rated surge voltage	6 kV
---------------------	------

Overvoltage category (EN 60950-1)	III
-----------------------------------	-----

Mechanical data | Material data

Coating contact	silver-plated
-----------------	---------------

Combustibility class (UL94)	V-0
-----------------------------	-----

Material housing	PC
------------------	----

Material contact	Brass
------------------	-------

Mechanical data | Mounting data

Number of module slots	1
------------------------	---

Height	35,5 mm
--------	---------

Width	34,1 mm
-------	---------

Depth	14,6 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	125 °C
----------------------------	--------