

PE-Female module, 1-pole, axial screw t.

1000 V, 200 A

Female

PE

Axial screw connection


Technical data will be only guaranteed with Murrelektronik components.

Axial screw connection only for flexible wires

The clip 70MH-ZZ100-0000000 is needed (4×)

[Link to Product](#)**Illustration**

Product may differ from Image

**Commercial data**

ECLASS-6.0	27143424
ECLASS-7.0	27440209
ECLASS-8.0	27440209
ETIM-5.0	EC000438
customs tariff number	85366990
GTIN	4048879663915
Packaging unit	1

Electrical data | Supply

Operating current	200 A
-------------------	-------

Installation

Connection cross section min.	25 mm ²
Connection cross section max.	70 mm ²
AWG number min.	3
AWG number max.	0

Installation | Connection

Stripping length	16 mm
Wire insulation diameter variable max.	max. 12 mm (25 mm ²); 16 mm (40 mm ²)
Connection information	Axial screw connection
Tightening torque	(25...70 mm ²); 9 Nm (70 mm ²)
Tightening torque	8 Nm
Gender	female
Width across flats	SW5
Mating cycles min.	500

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2024-05-06

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Installation | Pin assignment

No. of poles	PE
--------------	----

Device protection | Electrical

Pollution Degree	3
------------------	---

Mechanical data | Material data

Coating contact	silver-plated
-----------------	---------------

Combustibility class (UL94)	V-0
-----------------------------	-----

Material housing	PC
------------------	----

Material contact	Brass
------------------	-------

Mechanical data | Mounting data

Number of module slots	2
------------------------	---

Height	61,1 mm
--------	---------

Width	34,3 mm
-------	---------

Depth	29,3 mm
-------	---------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
----------------------------	--------

Operating temperature max.	125 °C
----------------------------	--------