

**M12 male 0° / M12 female 0° A-cod.**

TPE 5x18AWG ye UL/CSA. ITC/PLTC 2m

Male straight – female straight

Cable is approved for 600 V

M12 – M12, 5-pole



USA

Cable is approved for 600 V

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)**Illustration**



Product may differ from Image



|                                     |                   |
|-------------------------------------|-------------------|
| Cable length                        | 2 m               |
| Side 1                              |                   |
| Tightening torque                   | 0,6 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Coding                              | A                 |
| No. of poles                        | 5                 |
| Width across flats                  | SW13              |
| Degree of protection (EN IEC 60529) | IP65, IP66K, IP67 |
| Side 2                              |                   |
| Tightening torque                   | 0,6 Nm            |
| Mounting method                     | inserted, screwed |
| Family construction form            | M12               |
| Thread                              | M12 x 1           |
| Coding                              | A                 |
| No. of poles                        | 5                 |
| Width across flats                  | SW13              |
| Commercial data                     |                   |
| ECLASS-6.0                          | 27279218          |
| ECLASS-7.0                          | 27279218          |
| ECLASS-8.0                          | 27279218          |
| ECLASS-9.0                          | 27060311          |
| ECLASS-10.1                         | 27060311          |
| ECLASS-11.1                         | 27060311          |
| ECLASS-12.0                         | 27060311          |
| ETIM-5.0                            | EC001855          |
| customs tariff number               | 85444290          |
| GTIN                                | 4048879531412     |
| Packaging unit                      | 1                 |
| Electrical data   Supply            |                   |
| Operating voltage AC max.           | 125 V             |

|                                    |       |
|------------------------------------|-------|
| Operating voltage DC max.          | 125 V |
| Operating voltage AC (UL-listed)   | 30 V  |
| Operating voltage DC (UL-listed)   | 30 V  |
| Current operating per contact max. | 4 A   |

#### Device protection | Electrical

|  |                   |
|--|-------------------|
| Additional condition protection degree | inserted, screwed |
| Pollution Degree                       | 3                 |
| Rated surge voltage                    | 1,5 kV            |
| Material group (IEC 60664-1)           | I                 |

#### Mechanical data

|                             |         |
|-----------------------------|---------|
| Contour for corrugated hose | without |
|-----------------------------|---------|

#### Mechanical data | Material data

|                  |                  |
|------------------|------------------|
| Coating locking  | Nickeled         |
| Material housing | PUR              |
| Locking material | Zinc die-casting |

#### Mechanical data | Mounting data

|                 |                                       |
|-----------------|---------------------------------------|
| Mounting method | inserted, screwed, Shaking protection |
|-----------------|---------------------------------------|

#### Environmental characteristics | Climatic

|  |                            |
|--|----------------------------|
| Operating temperature min.             | -25 °C                     |
| Operating temperature max.             | 85 °C                      |
| Additional condition temperature range | depending on cable quality |

#### Important installation notes

|                        |   |
|------------------------|---|
| Note on strain relief  | Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.   |
| Note on bending radius | <b>Attention:</b> Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces. |

#### Conformity

|                  |                          |
|------------------|--------------------------|
| Product standard | DIN EN 61076-2-101 (M12) |
|------------------|--------------------------|

#### Installation | Cable

|  |   |
|--|---|
| Cable identification                     | 161                                     |
| Jacket Color                             | yellow                                  |
| Type of Certificate                      | cURus                                   |
| Amount stranding                         | 1                                       |
| Stranding                                | 5 wires around Core filler twisted      |
| Filler                                   | yes                                     |
| wire arrangement                         | brown, black, blue, white, green-yellow |
| Cable weight                             | 103,4 g/m                               |
| Material jacket                          | TPE                                     |
| Freedom from ingredients (jacket)        | lead-free, CFC-free, halogen-free       |
| Outer-diameter (jacket)                  | 7,75 mm                                 |
| Tolerance outer diameter (sheath)        | ± 5 %                                   |
| Material wire insulation                 | PVC                                     |
| Amount wires                             | 5                                       |
| Outer diameter insulation                | 1,93 mm                                 |
| Outer diameter tolerance core insulation | ± 5 %                                   |
| Ingredient freeness wire insulation      | lead-free, CFC-free                     |
| Amount strands (wire)                    | 19                                      |
| Diameter of single wires                 | 18 AWG                                  |
| Conductor crosssection (wire)            | 18 AWG                                  |
| Material conductor wire                  | Stranded copper wire, bare              |
| Nominal voltage AC max.                  | 600 V                                   |
| Current load capacity (standard)         | to DIN VDE 0298-4                       |

|   |  |
|---|--|
| Current load capacity min. wire                   | 9 A  |
| Electrical resistance line constant wire          | 22,5 $\Omega$ /km                                    |
| AC withstand voltage (wire - wire)                | 4 kV @ 60 s  |
| Power frequency withstand voltage (wire - jacket) | 4 kV @ 60 s  |
| Min. operating temperature (static)               | -40 °C   |
| Max. operating temperature (fixed)                | 105 °C   |
| Operating temperature min. (dynamic)              | -20 °C   |
| Operating temperature max. (dynamic)              | 90 °C  |
| Flame resistance                                  | UL 1581 § 1100 FT2   UL 1581 § 1090   IEC 60332-2-2  |
| chemical resistance                               | Good, application-related testing                    |
| Gasoline resistance                               | Good, application-related testing                    |
| Oil resistance                                    | DIN EN 60811-404   Good, application-related testing |
| Bending radius (fixed)                            | 10 x Outer diameter                                  |
| Bending radius (dynamic)                          | 15 x Outer diameter                                  |
| Travel speed (C-track)                            | 10 Mio.  |
| No. of torsion cycles                             | 3 Mio.   |
| Torsion stress                                    | $\pm 180$ °/m  |