

Power Supply Emparro20-Advanced-3-phase

IN: 3x400 - 500VAC; OUT: 45 - 56V/10ADC

The Emparro20-Advanced series of three-phase DIN rail power supplies are extremely versatile and are suitable for a wide range of applications where reliable DC power is required. The high efficiency of these power supplies allows you to save on energy costs while reducing your carbon footprint. Thanks to the low heat dissipation, the service life of the power supplies is extended and the cooling requirements of your control cabinet are reduced. The switching power supply also offers a 5-second power boost, which allows the operation of capacitive and inductive loads. With a very low inrush current, the input circuit breaker is prevented from tripping. The push-in terminal technology ensures quick and easy installation of the power supply unit. The powerful overvoltage protection effectively protects the power supplies from short-term voltage spikes, which extends the service life of the power supplies and increases machine availability.

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
customs tariff number	85044083
GTIN	4065909055250
Packaging unit	1
Electrical data	
Number of devices parallel connection max.	3
Number of devices series connection max.	20
Parallel connection	yes
Series connection	yes

Security level SELV/PELV

Electrical data | Supply

Power frequency 50/60 Hz

Electrical data | Input

Input voltage 1 AC	400 V
Input voltage 2 AC	500 V
Input voltage AC min.	350 V
Input voltage AC max.	575 V
Input current at input voltage 1 AC	0,8 A
Input current at input voltage 2 AC	0,65 A
Phase number input	3
Efficiency	95,3 % @ 400 V AC, 95,1 % @ 500 V AC

Electrical data | Output

Duration Power Boost max.	5 s
Output rating	480 W
Output voltage DC	48 V
Output voltage DC min.	45 V
Output voltage DC max.	56 V
Output current	10,6 A
Output current min.	8,6 A
Output current max.	10,6 A
Mains failure bridging time	25 ms
Power Boost	150 %
Ripple (s-s) max.	50 mV
Spikes (s-s) max.	120 mV

Diagnostics

Alarm contact yes

Installation | Connection

Connection Push-In spring clamp terminals

Device protection | Electrical

Installation height max. ASL	3000 m
Degree of protection (EN IEC 60529)	IP20
Protection class (EN IEC 61140)	I
Overload protection output	yes
Invers-polarity protection	no
Pollution Degree	2
Short-circuit protection output	yes
Overttemperature protection output	yes

Device protection | Mechanical

Cooling type	Natural convection
Shock resistance (EN IEC 60068-2-27)	30 g, 11 ms 3 x (X-, Y-, Z-axis)
Vibration resistance (EN IEC 60068-2-6)	2 g (10 ... 500 Hz), 1 h / direction (X-, Y-, Z-axis)

Mechanical data | Material data

Combustibility class housing (UL94)	V-0
Conformal coated PCB	no
Material housing	Aluminium

Mechanical data | Mounting data

Net weight	1050 g
Mounting method	geschnappt
Suitable for mounting type	Tragschiene TH35-7.5/TH35-15

mounting position	horizontal, vertical
Height	135,7 mm
Width	65 mm
Depth	159,3 mm

Environmental characteristics | Climatic

Ambient temperature min.	-25 °C
Ambient temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Relative humidity max. (operation)	95 % no condensation

Environmental product conformity

REACH	(EC) No 1907/2006
REACH-SVHC	compliant
RoHS	2011/65/EU
China RoHS	compliant EPUP 25
WEEE	compliant
Halogen-free-Material	JEDEC JS709A
Pb-free-Material	JESD97

Conformity

CE	2014/30/EU
----	------------

Approvals

UL	E200364
ULc	E200364
SEMI F47	compliant